

Fluke Endüstriyel Test Aletleri

Tavsiye Edilen Son Kullanıcı Fiyat Listesi

Türkiye

FLUKE®

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numar:	Ürün Tanımı
Dijital Multimetreler					
110 Serisi Multimetreler					
Fluke 113	True RMS Multimeter	TL	336	FLUKE-113 EUR	FLUKE-113 EUR,UTILITY MULTIMETER (EUR)
Fluke 114	True RMS Multimeter	TL	368	FLUKE-114 EUR	FLUKE-114 EUR,ELECTRICAL TRMS MULTIMETER (EUR)
Fluke 115	True RMS Multimeter	TL	451	FLUKE-115 EUR	FLUKE-115 EUR,TRUE RMS MULTIMETER (EUR)
Fluke 116	True RMS Multimeter	TL	508	FLUKE-116 EUR	FLUKE-116 EUR,HVAC TRUE RMS MULTIMETER (EUR)
Fluke 117	True RMS Multimeter	TL	540	FLUKE-117 EUR	FLUKE-117 EUR,ELECTRICIANS TRUE RMS MULTIMETER (EUR)
C50	Soft Meter Case	TL	91	C50	C50,CARRYING CASE
170 Serisi Multimetreler					
Fluke 175	True RMS Multimeter	TL	679	FLUKE-175 EGFID	FLUKE-175 EGFID,TRMS MULTIMETER (ENG, GER, FR, ITA, DUT)
Fluke 177	True RMS Multimeter	TL	704	FLUKE-177 EGFID	FLUKE-177 EGFID,TRMS MULTIMETER W/BACKLIGHT (ENG, GER, FR, ITA, DUT)
Fluke 179	True RMS Multimeter	TL	734	FLUKE-179 EGFID	FLUKE-179 EGFID,TRMS MULTIMETER W/BACKLIGHT & TEMP (ENG, GER, FR, ITA, DUT)
Fluke 179/MAG2 Kit	Industrial Combo Kit	TL	842	FLUKE- 179/MAG2	FLUKE-179/MAG2,ELECTRICIAN DMM, FLASHLIGHT, AND DELUXE ACCESSORY COMBO KIT
Fluke 179/TPAK	179/ToolPak Combo Kit	TL	773	FLK- 179/TPAK EGFID	FLK-179/TPAK EGFID,FLUKE-179 WITH TPAK EGFID
Fluke 179/EDA2/EUR	Electronics Combo Kit	TL	819	FLUKE- 179/EDA2/E UR	FLUKE-179/EDA2/EUR,ELECTRONICS DMM AND DELUXE ACCESSORY COMBO KIT, EUROPE
Fluke 179/TPAK/EUR	179/Toolpak Combo Kit	TL	762	FLUKE- 179/TPAK/E UR	FLUKE-179/TPAK/EUR,FLUKE-179 WITH TPAK, EUROPE
C90	Soft Meter Case	TL	91	C90	C90,CARRYING CASE
200 Serisi Multimetreler					
Fluke 233	Remote Display Multimeter	TL	798	FLUKE-233 EU	FLUKE-233 EU,REMOTE DISPLAY TRUE RMS MULTIMETER EUROPE
Fluke 287/EUR	True RMS Electronic Logging Multimeter with TrendCapture	TL	1288	FLUKE- 287/EUR	FLUKE-287/EUR,TRUE-RMS ELECTRONIC LOGGING MULTIMETER WITH TRENDCAPTURE, EUROPE
Fluke 287/FVF/EUR	FlukeView Forms Combo Kit	TL	1619	FLUKE- 287/FVF/EU R	FLUKE-287/FVF/EUR,TRUE-RMS ELECTRONIC LOGGING MULTIMETER WITH TRENDCAPTURE, EURO

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke 289/EUR	True RMS Industrial Logging Multimeter with TrendCapture	TL	1507	FLUKE-289/EUR	FLUKE-289/EUR,TRUE-RMS INDUSTRIAL LOGGING MULTIMETER WITH TRENDCAPTURE, EUROPE
Fluke 289/FVF/EUR	Industrial Logging Multimeter and Software Combo Kit	TL	1706	FLUKE-289/FVF/EUR	FLUKE-289/FVF/EUR,TRUE-RMS INDUSTRIAL LOGGING DMM W/TRENDCAPTURE, FVF S/W, EURO
C280	Soft Meter Case	TL	87	C280	C280,CARRYING CASE, POLYESTER, BLK/YEL

20 Serisi Multimetreler

Fluke 27II/EUR	Industrial Multimeter (IP67)	TL	1162	FLUKE-27II/EUR	FLUKE-27II/EUR,AVG MULTIMETER, EUROPE
Fluke 28II/EUR	True RMS Industrial Multimeter (IP67)	TL	1189	FLUKE-28II/EUR	FLUKE-28II/EUR,TRMS MULTIMETER, EUROPE
Fluke 28 II Ex	Intrinsically safe true-rms digital multimeter	TL	2905	FLUKE-28IIEX	FLUKE-28IIEX,INTRINSICALLY SAFE VERSION OF 28II WITH ATEX APPROVAL
C25	Soft Meter Case	TL	91	C25	C25,SOFT CASE FOR FLUKE-25/27/8025A

70 Serisi Multimetreler

Fluke 77-4/EUR	Multimeter	TL	709	FLUKE-77-4/EUR	FLUKE-77-4/EUR,INDUSTRIAL MULTIMETER, 1000V CAT III, EUROPE
C90	Soft Meter Case	TL	91	C90	C90,CARRYING CASE

80 Serisi Multimetreler

Fluke 83-V/EUR	Multimeter	TL	1006	FLUKE-83-5/EUR	FLUKE-83-5/EUR,INDUSTRIAL MULTIMETER, EUROPE
Fluke 87V/i410	Combo Kit for Industrial	TL	1562.04832	FLUKE-87V/i410	FLUKE-87V/i410,FLUKE-87V DMM AND I410 CURRENT CL
Fluke 87-V/EUR	True RMS Multimeter	TL	1031	FLUKE-87-5/EUR	FLUKE-87-5/EUR,INDUSTRIAL TRUE RMS MULTIMETER, EUROPE
Fluke 87-V/E2K/EUR	Industrial Electricians Combo Kit	TL	1169	FLUKE-87-5/E2K/EUR	FLUKE-87-5/E2K/EUR,INDUSTRIAL TRUE-RMS MULTIMETER COMBO KIT, EUROPE
C25	Soft Meter Case	TL	91	C25	C25,SOFT CASE FOR FLUKE-25/27/8025A

Bench Multimetreler

Fluke 8808A 220V	5.5 Digit Multimeter	TL	1978	8808A 220V	8808A 220V,5.5 DIGIT PRECISION MULTIMETER
Fluke 8808A 240V	5.5 Digit Multimeter	TL	1978	8808A 240V	8808A 240V,5.5 DIGIT PRECISION MULTIMETER
Fluke 8808A/SU 240V	5.5 Digit Multimeter (software & cable)	TL	2516	8808A/SU 240V	8808A/SU 240V, 5.5 DIGIT PRECISION MULTIMETER, SW & CABLE
Fluke 8808A/SU 220V	5.5 Digit Multimeter (software & cable)	TL	2516	8808A/SU 220V	8808A/SU 220V,5.5 DIGIT PRECISION MULTIMETER, SW & CABLE
Fluke 8808A/TL 240V	5.5 Digit Multimeter, 2X4W Test Lead Kit	TL	2184	8808A/TL 240V	8808A/TL 240V,5.5 DIGIT MULTIMETER
Fluke 8808A/TL 220V	5.5 Digit Multimeter, 2X4W Test Lead Kit	TL	2184	8808A/TL 220V	8808A/TL 220V,5.5 DIGIT MULTIMETER
Fluke 8845A 240V	6.5 Digit Precision Multimeter	TL	2539	8845A 240V	8845A 240V, 6.5 DIGIT PRECISION MULTIMETER, 35PPM

Model	Açıklama	Para Birimi	Tavsiye edilen		Ürün Tanımı
			Son Kullanıcı	Parça numar:	
			Liste fiyatı		
Fluke 8845A 220V	6.5 Digit Precision Multimeter	TL	2539	8845A 220V	8845A 220V, 6.5 DIGIT PRECISION MULTIMETER, 35PPM
Fluke 8845A/SU 240V	6.5 Digit Precision Multimeter (incl. software + cable)	TL	3042	8845A/SU 240V	8845A/SU 240V,6.5 DIGIT PRECISION MULTIMETER, SW & CABLE
Fluke 8845A/SU 220V	6.5 Digit Precision Multimeter (incl. software + cable)	TL	3042	8845A/SU 220V	8845A/SU 220V,6.5 DIGIT PRECISION MULTIMETER, SW & CABLE
Fluke 8846A 240V	6.5 Digit Precision Multimeter	TL	3556	8846A 240V	8846A 240V, 6.5 DIGIT PRECISION MULTIMETER, 24PPM USBMEM
Fluke 8846A	6.5 Digit Precision Multimeter	TL	3556	8846A 220V	8846A 220V, 6.5 DIGIT PRECISION MULTIMETER, 24PPM USBMEM
Fluke 8846A/SU 240V	6.5 Digit Precision Multimeter (incl. software + cable)	TL	4071	8846A/SU 240V	8846A/SU 240V,6.5 DIGIT PRECISION MULTIMETER, SW & CABLE
Fluke 8846A/SU 220V	6.5 Digit Precision Multimeter (incl. software + cable)	TL	4071	8846A/SU 220V	8846A/SU 220V,6.5 DIGIT PRECISION MULTIMETER, SW & CABLE
884X-CASE	Hard Case (8845A/8846A)	TL	755	884X-CASE	884X-CASE,HEAVY DUTY BLACK CASE
884X-ETH	Ethernet Interface Cable	TL	44	884X-ETH	884X-ETH,ETHERNET INTERFACE CABLE
884X-RTD	100 OHM RTD Temperature Probe	TL	1269	884X-RTD	884X-RTD,100 OHM RTD TEMPERATURE PROBE
884X-SHORT	4-wire short	TL	77	884X-SHORT	884X-SHORT,4 WIRE SHORT
884X-USB	USB to RS232 Cable Adapter	TL	384	884X-USB	884X-USB,USB TO RS232 CABLE ADAPTER
884X-1G	USB Memory 1 GB	TL	318	884X-1G	884X-1G,USB MEMORY 1 GB
8845A-EFPT	Extended Fiine Point Tip Adapter Set	TL	33	8845A-EFPT	8845A-EFPT,EXTENDED FINE PT TIP ADAP SET (SET RED/BLACK)
8845A-TPIT	Test Probe IC Tip Set	TL	33	8845A-TPIT	8845A-TPIT,TEST PROBE IC TIP (SET RED & BLACK)
FVF-UG	FlukeView Forms Upgrade	TL	286	FVF-UG	FVF-UG,FLUKEVIEW FORMS UPGRADE
FVF-SC4	FlukeView Forms Software + Cable (8845A/8846A)	TL	727	FVF-SC4	FVF-SC4,FLUKEVIEW FORMS W/CABLE FOR 8845/8846
FVF-SC5	FlukeView Forms Basic (8845A/8846A)	TL	313	FVF-SC5	FVF-SC5,FLUKEVIEW FORMS - BASIC FOR 8845/8846
RS43	Serial Interface Cable	TL	146	RS43	RS43,SERIAL INTERFACE CABLE
TL2X4W-PTII	2x4 Wire Ohms Test Lead 2 mm Probe Tip	TL	197	TL2X4W-PTII	TL2X4W-PTII,2X4 WIRE OHMS 1000V TEST LEAD
TL2x4W-TWZ	2X4-Wire Ohms Tweezers Test Leads	TL	252	TL2X4W-TWZ	TL2X4W-TWZ,2X4 WIRE OHMS SMD TEST TWEEZER
Y8021	IEEE-488 Shielded Interface Cable, 1 m	TL	691	Y8021	Y8021,IEEE-488 SHIELDED INTERFACE CABLE, 1M

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Y8022	IEEE-488 Shielded Interface Cable, 2 m	TL	835	Y8022	Y8022,IEEE-488 SHIELDED INTERFACE CABLE, 2M
Y8846S	Rack mount kit single (8845A/8846A)	TL	242	Y8846S	Y8846S,RACK MOUNT KIT 8845A & 8846A SINGLE
Y8846D	Rack mount kit dual (8845A/8846A)	TL	318	Y8846D	Y8846D,RACK MOUNT KIT 8845A & 8846A DUAL
FVF-SC3	FlukeView Forms Software + Cable (Fluke 45)	TL	576	FVF-SC3	FVF-SC3,FLUKEVIEW FORMS W/CABLE FOR 45 DMM

Otomotiv Test Cihazları

Fluke 88V/A	Automotive Meter Combo Kit	TL	1589	FLUKE-88-5/A KIT	FLUKE-88-5/A KIT,AUTOMOTIVE METER COMBO KIT
-------------	----------------------------	----	------	------------------	---------------------------------------------

Pens Ampermetreler

Fluke 323	True RMS Clamp Meter	TL	309	FLUKE-323	FLUKE-323,400A AC TRUE RMS CLAMP METER
Fluke 324	True RMS Clamp Meter	TL	398	FLUKE-324	FLUKE-324,400A AC TRUE RMS CLAMP METER W/TEMP
Fluke 325	True RMS Clamp Meter	TL	560	FLUKE-325	FLUKE-325,400A AC/DC TRUE RMS CLAMP METER W/TEMP
Fluke 353	AC/DC True RMS Clamp Meter	TL	1718	FLUKE-353	FLUKE-353,AC/DC TRMS CLAMP METER,2000A,AMPS ONLY
Fluke 355	AC/DC True RMS Clamp Meter	TL	2063	FLUKE-355	FLUKE-355,AC/DC TRMS CLAMP METER,2000A
Fluke 360	Leakage Current Clamp Meter	TL	1887	FLUKE-360	FLUKE-360,LEAKAGE CURRENT CLAMP METER
Fluke 365	Detachable TRMS Clamp Meter	TL	668	FLUKE-365/E	FLUKE-365/E,DETACHABLE 200A TRMS AC/DC CLAMP
Fluke 373	600A TRMS Clamp Meter	TL	531	FLUKE-373/E	FLUKE-373/E,600A TRMS AC CLAMP METER
Fluke 374	600A TRMS Clamp meter	TL	732	FLUKE-374/E	FLUKE-374/E,600A TRMS AC/DC CLAMP
Fluke 375	600A TRMS Clamp Meter	TL	883	FLUKE-375/E	FLUKE-375/E,600A TRMS AC/DC CLAMP
Fluke 376	TRMS Clamp meter	TL	1047	FLUKE-376/E	FLUKE-376/E,1000A TRMS AC/DC CLAMP W/IFLEX
Fluke 381	Remote Display TRMS Clamp Meter	TL	1331	FLUKE-381	FLUKE-381, REMOTE DISP 1000A TRMS CLAMP W/IFLEX
Fluke 902/E	True RMS Clamp Meter (HVAC)	TL	707	FLUKE-902/E	FLUKE-902/E,TRMS CLAMP METER FOR EUROPE
Fluke i2500-18	iFlex Probe	TL	348	FLUKE-I2500-18	FLUKE-I2500-18, IFLEX 2500A PROBE 18IN
Fluke i2500-10	iFlex Probe	TL	348	FLUKE-I2500-10	FLUKE-I2500-10, IFLEX 2500A PROBE 10IN
H3	Holster (330 Series)	TL	82	H3	H3,HOLSTER WITH ACCESSORY POCKET,333 - 337 CLAMP METERS

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
-------	----------	-------------	-------------------------------------------------	--------------	-------------

CNX Kablosuz Sistem

Fluke CNX 3000	CNX Wireless Digital Multimeter	TL	915	FLK-CNX 3000	FLK-CNX 3000,CNX WIRELESS DIGITAL MULTIMETER
Fluke CNX i3000	CNX Wireless iFlex AC Current Module	TL	521	FLK-CNX I3000	FLK-CNX I3000,CNX WIRELESS IFLEX AC CURRENT MODULE
Fluke CNX a3000	CNX Wireless AC Current Clamp Module	TL	444	FLK-CNX A3000	FLK-CNX A3000,CNX WIRELESS AC CURRENT CLAMP MODULE
Fluke CNX v3000	CNX Wireless AC Voltage Module	TL	444	FLK-CNX V3000	FLK-CNX V3000,CNX WIRELESS AC VOLTAGE MODULE
Fluke CNX t3000	CNX Wireless K-Type Temperature Module	TL	444	FLK-CNX T3000	FLK-CNX T3000,CNX WIRELESS K-TYPE TEMPERATURE MODULE
Fluke CNX pc3000	CNX Wireless PC Adapter	TL	130	FLK-CNX PC3000	FLK-CNX PC3000,CNX WIRELESS PC ADAPTER
Fluke CNX 3000 ind	CNX Wireless Industrial System	TL	2612	FLK-CNX 3000 IND	FLK-CNX 3000 IND,CNX WIRELESS INDUSTRIAL SYSTEM
Fluke CNX 3000 gm	CNX Wireless General Maintenance System	TL	1830	FLK-CNX 3000 GM	FLK-CNX 3000 GM,CNX WIRELESS GENERAL MAINTENANCE SYSTEM
Fluke CNX 3000 HVAC	CNX Wireless HVAC System	TL	1567	FLK-CNX 3000 HVAC	FLK-CNX 3000 HVAC,CNX WIRELESS HVAC SYSTEM
Fluke CNX t3000 KIT	CNX Wireless Basic Kit with t3000	TL	1176	FLK-CNX T3000 KIT	FLK-CNX T3000 KIT,CNX WIRELESS BASIC KIT WITH T3000
Fluke CNX i3000 KIT	CNX Wireless Basic Kit with i3000	TL	1306	FLK-CNX I3000 KIT	FLK-CNX I3000 KIT,CNX WIRELESS BASIC KIT WITH I3000
Fluke CNX a3000 KIT	CNX Wireless Basic Kit with a3000	TL	1176	FLK-CNX A3000 KIT	FLK-CNX A3000 KIT,CNX WIRELESS BASIC KIT WITH A3000
Fluke CNX v3000 KIT	CNX Wireless Basic Kit with v3000	TL	1176	FLK-CNX V3000 KIT	FLK-CNX V3000 KIT,CNX WIRELESS BASIC KIT WITH V3000
Fluke CNX c3001	CNX Module Soft Case	TL	50	FLK-CNX C3001	FLK-CNX C3001,CNX MODULE SOFT CASE
Fluke CNX c3000	CNX Premium Modular Tool Bag	TL	261	FLK-CNX C3000	FLK-CNX C3000,CNX PREMIUM MODULAR TOOL BAG
Fluke CNX c3002	CNX DMM Soft Case	TL	80	FLK-CNX C3002	FLK-CNX C3002,CNX DMM SOFT CASE
Fluke CNX c3003	CNX 3-Compartment Soft Case	TL	105	FLK-CNX C3003	FLK-CNX C3003,CNX 3-COMPARTMENT SOFT CASE

Elektriksel Test Cihazları

Fluke 1AC II	Volt Alert	TL	73	FLUKE-1AC-E2-II	FLUKE-1AC-E2-II,ACV DETECTOR 200-1000V, ENG, FIN, E. SPN, PORT, ITA
Fluke 1AC II 5PK	Volt Alert 5-pack	TL	309	FLK-1AC-E1-II-5PK	FLK-1AC-E1-II-5PK,VOLT ALERT, 5 PACK, ENG, E. FRN, E. SPN
Fluke T5-600	Electrical Tester	TL	261	T5-600 EUR1	T5-600 EUR1,ELECTRICAL TESTER, ROUND
Fluke T5-600/62MAX+/1A C kit	Electrical Tester, IR Thermometer and Voltage Detector Kit	TL	602	T5-600/62MAX+/1ACE	T5-600/62MAX+/1ACE,KIT WITH T5-600, 62MAX+, 1AC II, EUROPE VERSION
Fluke T5-1000	Electrical Tester	TL	366	T5-1000 EUR1	T5-1000 EUR1,ELECTRICAL TESTER, ROUND

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke T5-H5-1AC II Kit	Electrical Tester Kit with Holster and 1AC	TL	478	T5-H5-1AC KIT/EUR	T5-H5-1AC KIT/EUR,T5-1000 EUR1 ELE TESTER,H5 HOLS,FLUKE-1AC-E4 KIT
Fluke T50	Voltage/Continuity Tester	TL	126	T50	T50,VOLTAGE TESTER
Fluke T100	Voltage/Continuity Tester	TL	172	T100	T100,VOLTAGE/CONTINUITY TESTER
Fluke T120	Voltage/Continuity Tester	TL	286	T120	T120,VOLTAGE/CONTINUITY TESTER WITH LCD
Fluke SM100	Socket Tester	TL	69	FLUKE-SM100	FLUKE-SM100,SOCKETMASTER
Fluke SM200	Socket Tester	TL	91	FLUKE-SM200	FLUKE-SM200,SOCKETMASTER PLUS
Fluke SM300	Socket Tester	TL	149	FLUKE-SM300	FLUKE-SM300,SOCKETMASTER ADVANCED
Fluke 2042	Cable Locator (Transmitter + Receiver)	TL	2132	FLUKE-2042	FLUKE-2042,CABLE LOCATOR SET
Fluke 2042T	Cable Locator Transmitter	TL	1052	FLUKE-2042T	FLUKE-2042T,CABLE LOCATOR TRANSMITTER
Fluke 9040EUR	Phase Rotation Indicator	TL	533	FLUKE-9040EUR	FLUKE-9040EUR,PHASE ROTATION INDICATOR, EUROPE
Fluke 9062	Motor and Phase Rotation Indicator	TL	533	FLUKE-9062	FLUKE-9062,CONTACTLESS PHASE SEQUENCE INDICATOR
LVD1	Volt Light	TL	66	LVD1	LVD1,VOLT LIGHT
LVD2	Volt Light	TL	91	LVD2	LVD2,VOLT LIGHT
H5	Electrical Tester Holster (Fluke T5)	TL	75	H5	H5,HOLSTER,BELT,ACCESSORY
FLK2AC/200-1000VCL	ACV Detector 200-1000V	TL	71	FLK2AC/200-1000VCL	FLK2AC/200-1000VCL,ACV DETECTOR 200-1000V, COUNTER TOP, ENG, FIN, SPN, ITA

Lazerli Mesafe Ölçüm Cihazı

Fluke 414D	Laser Distance Meter	TL	320	FLUKE-414D	FLUKE-414D,LASER DISTANCE METER - 50M/165FT MAX
Fluke 419D	Laser Distance Meter	TL	640	FLUKE-419D	FLUKE-419D,LASER DISTANCE METER - 80M/260FT MAX
Fluke 424D	Laser Distance Meter	TL	961	FLUKE-424D	FLUKE-424D,LASER DISTANCE METER - 100M/330FT MAX

İzolasyon Test Cihazı

Fluke 1503	Insulation Tester	TL	1123	FLUKE-1503	FLUKE-1503,INSULATION TESTER
Fluke 1507	Insulation Tester	TL	1278	FLUKE-1507	FLUKE-1507,INSULATION TESTER
Fluke 1550C	Insulation Resistance Tester (5kV)	TL	7995	FLUKE-1550C	FLUKE-1550C,5KV INSULATION TESTER
Fluke 1550C/Kit	Insulation Resistance Tester Kit (5kV)	TL	8965	FLUKE-1550C/KIT	FLUKE-1550C/KIT,5KV INSULATION TESTER KIT
Fluke 1555	Insulation Resistance Tester (10kV)	TL	9937	FLUKE-1555	FLUKE-1555,10KV INSULATION TESTER
Fluke 1555/Kit	Insulation Resistance Tester Kit (10kV)	TL	11149	FLUKE-1555/KIT	FLUKE-1555/KIT,10KV INSULATION TESTER KIT
Fluke 1577	Insulation Multimeter	TL	1468	FLUKE-1577	FLUKE-1577,INSULATION MULTIMETER
Fluke 1587	Insulation Multimeter	TL	1743	FLUKE-1587	FLUKE-1587,INSULATION MULTIMETER

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke 1587/ET Kit	Fluke 1587/ET Advanced Electrical Troubleshooting Kit	TL	2351	Fluke 1587/ET Kit	
Fluke 1587T	Insulation Multimeter (Telecom)	TL	1866	FLUKE-1587 T	FLUKE-1587 T,INSULATION MULTIMETER
Fluke 1587MDT	Advanced Motor & Drive Troubleshooting Kit	TL	2550	FLUKE-1587 MDT	FLUKE-1587 MDT,ADVANCED MOTOR AND DRIVE TROUBLESHOOTING KIT
FVF-Basic	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	TL	359	FVF-BASIC	FVF-BASIC,FLUKEVIEW FORMS W/CABLE FOR 180 SERIES AND 789
FVF-SC2	FlukeView Forms Software + IR USB- Cable (180 Series, 1653, 789, 1550B)	TL	560	FVF-SC2	FVF-SC2,FLUKEVIEW FORMS WITH CABLE FOR USE WITH 18X, 28X DMMS
IR189USB	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	TL	133	IR189USB	IR189USB, USB CABLE FOR FLUKE-18X, 28X DMMS

Elektriksel Tesisat Test Cihazı

Fluke 1653B	Multifunction Installation Tester	TL	3936	FLUKE- 1653B-05	FLUKE-1653B-05,INSTALLATION TESTER W/AUTOTEST, MEM, EUR,SCHUKO
Fluke 1654B-05	Installation Tester, W/ RCD Type B	TL	4858	FLUKE- 1654B-05	FLUKE-1654B-05, INSTALLATION TESTER W/RCD TYPE B, MEM, GENERIC,SCHUKO
Fluke 1652C-05	Installation Tester, W/Phase sequence	TL	2975	FLUKE- 1652C-05	FLUKE-1652C-05, INSTALLATION TESTER W/PHASE SEQUENCE,GENERIC SCHUKO CORD
FLUKE-1654B- 05/FVF	Installation Tester with FVF	TL	5388	FLUKE- 1654B- 05/FVF	FLUKE-1654B-05/FVF,1654B-05, INST TESTER, GENERIC SCHUKO, FVF-SC2
Fluke 1653B- 05/FVF	Multifunction Installation Tester (incl. FlukeView)	TL	4352	FLUKE- 1653B- 05/FVF	FLUKE-1653B-05/FVF,1653B-05,INST TESTER, MEM, EUR, FVF-SC2
FVF-SC2	FlukeView Forms Software + IR USB- Cable (180 Series, 1653, 789, 1550B)	TL	560	FVF-SC2	FVF-SC2,FLUKEVIEW FORMS WITH CABLE FOR USE WITH 18X, 28X DMMS
ES165X	Earth Spike Test Kit	TL	448	ES165X	ES165X, EARTH SPIKE TEST KIT
IR189USB	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	TL	133	IR189USB	IR189USB, USB CABLE FOR FLUKE-18X, 28X DMMS
MTC77	Mains Test Cord (CEE 7 7 Schuko)	TL	158	MTC77	MTC77,MAINS TEST CORD FOR CEE 7 7 SCHUKO
TP165X	Remote Control Probe (1650 Series)	TL	183	TP165X	TP165X,TEST PROBE WITH REMOTE TEST BUTTON
ZERO ADAPTER	Zero adapter (165xB)	TL	82	ZERO ADAPTER	ZERO ADAPTER,ZERO ADAPTER FOR 165XB
TL165X	Standard Test Lead Set (1650 Series)	TL	265	TL165X	TL165X,STD TL SET W/LEADS,PROBES,CAPS,ALLIGATOR CLIPS

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Portatif Elektriksel Cihaz Test Aleti					
Fluke 6200	Portable Appliance Tester	TL	3595	FLUKE-6200	FLUKE-6200,PORTABLE APPLIANCE TESTER MPP UK
Fluke 6200/UK Kit	Fluke 6200 PAT Kit	TL	3796	FLUKE-6200/UK KIT	FLUKE-6200/UK KIT,PAT KIT 1 - PAT STARTER KIT
Fluke 6500	Portable Appliance Tester	TL	5041	FLUKE-6500	FLUKE-6500,PORTABLE APPLIANCE TESTER HPP UK
Fluke 6500/UK Kit	Fluke 6500 PAT Kit	TL	8039	FLUKE-6500/UK KIT	FLUKE-6500/UK KIT,PAT KIT 2 - PAT PROFESSIONAL KIT
APP1000	Barcode Appliance Number Labels 0-1000	TL	270	APP1000	APP1000, BARCODE APPLIANCE NUMBER LABELS 0 - 1000
APP2000	Barcode Appliance Number Labels 1001-2000	TL	270	APP2000	APP2000, BARCODE APPLIANCE NUMBER LABELS 1001 - 2000
AUTO200B	Auto Code Label	TL	119	AUTO200B	AUTO200B,LABEL, AUTO CODE UK
BDST3	Snap Tag (cable tie)	TL	96	BDST3	BDST3,SNAP TAGS (CABLE TIE)
EXTL100	Extension Lead Test Adaptor	TL	62	EXTL100	EXTL100,EXTENTION LEAD TEST ADAPTOR UK
IRP1	PAT Register	TL	23	IRP1	IRP1, REGISTER FOR PAT (LOG BOOK)
SP1000	Mini Printer	TL	1697	SP1000	SP1000,MINI PRINTER
SP1000PAPER	Paper Roll For SP1000	TL	23	SP1000PAPE R	SP1000PAPER, PAPER ROLL FOR SP1000
SPSCAN15	Barcode Scanner	TL	1553	SPSCAN15	SPSCAN15,WIDE HEAD SCANNER
TA700	Appliance Adaptor for 110V tools	TL	117	TA700	TA700,APPLIANCE ADAPTER FOR 110V TOOLS
PASS500S	Appliance Pass Labels (rectangular)	TL	89	PASS 500S	PASS 500S,APPLIANCE PASS LABELS,A5 SHEET ROUND
PASS560R	Appliance Pass Labels (round)	TL	94	PASS 560R	PASS 560R,APPLIANCE PASS LABELS 560,A5 SHEET ROUND

Portatif Elektriksel Cihaz Test Aleti

Fluke 1621	Earth Ground Tester	TL	1724	FLUKE-1621	FLUKE-1621,EARTH GROUND TESTER
Fluke 1623	Basic GEO Earth Ground Tester	TL	4119	FLUKE-1623	FLUKE-1623,BASIC GEO EARTH GROUND TESTER
Fluke 1623 Kit	Basic GEO Earth Ground Tester Kit	TL	6651	FLUKE-1623 KIT	FLUKE-1623 KIT,BASIC GEO EARTH GROUND TESTER
Fluke 1625	Advanced GEO Earth Ground Tester	TL	5994	FLUKE-1625	FLUKE-1625,ADVANCED GEO EARTH GROUND TESTER
Fluke 1625 Kit	Advanced GEO Earth Ground Tester Kit	TL	9459	FLUKE-1625 KIT	FLUKE-1625 KIT,ADVANCED GEO EARTH GROUND TESTER
Fluke 1630	Earth Ground Clamp Meter	TL	4249	FLUKE-1630	FLUKE-1630,EARTH GROUND CLAMP
EI-1623	Selective/stakeless clamp set (1623)	TL	1743	EI-1623	EI-1623,SELECTIVE/STAKELESS CLAMP SET FOR 1623,CONSISTS OF EI-162X AND EI-162AC
EI-1625	Selective/stakeless clamp set (1625)	TL	2182	EI-1625	EI-1625,A604510304,SELECTIVE/STAKELESS CLAMP SET,WITH EI-162X,EI-162AC AND 2-3 WIRE CABLE
EI-162BN	320 mm Split Core Transformer	TL	5468	EI-162BN	EI-162BN,A680506211,12.7 INCH (320MM) SPLIT CORE TRANSFORMER

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
ES-162P3	Stake/reel set for 3-pole measurement	TL	682	ES-162P3	ES-162P3,A604510302,STAKE SET FOR 3 POLE MEASUREMENT
ES-162P4	Stake/Reel Set for 4 pole measurements	TL	951	ES-162P4	ES-162P4,A604510301,STAKE SET FOR 4 POLE MEASUREMENT
GEO CABLE-REEL 25M	Ground Earth Cable Reel 25M Wire	TL	158	GEO CABLE-REEL 25M	GEO CABLE-REEL 25M,A604505102, GROUND/EARTH CABLE REEL 25M WIRE
GEO CABLE-REEL 50M	Ground Earth Cable Reel 50M Wire	TL	204	GEO CABLE-REEL 50M	GEO CABLE-REEL 50M,A604505103, GROUND/EARTH CABLE REEL 50M WIRE
GEO EARTH STAKE	Ground Earth Stake	TL	158	GEO EARTH STAKE	GEO EARTH STAKE,A604510350, GROUND/EARTH EARTH STAKE

Kapalı alan Hava Kalitesi Cihazları

Fluke 922	Airflow Meter	TL	1418	FLUKE-922	FLUKE-922, AIRFLOW METER
Fluke 922/Kit	Airflow Meter Kit	TL	1763	FLUKE-922/KIT	FLUKE-922/KIT, AIRFLOW METER KIT
Fluke 971	Temperature Humidity Meter	TL	659	FLUKE-971	FLUKE-971, TEMPERATURE HUMIDITY METER
Fluke 975	AirMeter	TL	7760	FLUKE-975	FLUKE-975, AIRMETER
Fluke 975V	AirMeter with Velocity	TL	8441	FLUKE-975V	FLUKE-975V, AIRMETER WITH VELOCITY PROBE
Fluke CO-220	Carbon Monoxide Meter	TL	972	FLUKE-CO-220	FLUKE-CO-220,CARBON MONOXIDE METER
Fluke RLD2	Leak Detector Flashlight	TL	128	RLD2	RLD2,LEAK DETECTOR FLASHLIGHT
CO-205	Aspirator Kit	TL	348	FLUKE-CO-205	FLUKE-CO-205,CARBON MONOXIDE ASPIRATOR KIT
975R	Regulator	TL	640	FLUKE-975R	FLUKE-975R, REGULATOR, 100-12P0.5
975VP	Air Velocity Probe	TL	1365	FLUKE-975VP	FLUKE-975VP, AIR VELOCITY PROBE
PT12	Pitot Tube, 12	TL	345	PT12	PT12,PITOT TUBE, 12 INCH
Fluke 985	Airborne Particle Counter	TL	11582	FLUKE-985	FLUKE-985, AIRBORNE PARTICLE COUNTER

Dijital Termometreler

Fluke 51 II	Thermometer	TL	634	FLUKE-51-2 50HZ	FLUKE-51-2 50HZ,SINGLE INPUT THERMOMETER (INTL VERSION), 50HZ NOISE REJECTION
Fluke 52 II	Thermometer	TL	750	FLUKE-52-2 50HZ	FLUKE-52-2 50HZ,DUAL INPUT THERMOMETER (INTL VERSION), 50HZ NOISE REJECTION
Fluke 53 II B	Single Input Thermometer, 60Hz	TL	842	FLUKE-53-2 B 60HZ	FLUKE-53-2 B 60HZ,SINGLE INPUT THERMOMETER W/USB RECORDING, 60HZ NOISE REJECTION
Fluke 53 II B	Single Input Thermometer, 50Hz	TL	828	FLUKE-53-2 B 50HZ	FLUKE-53-2 B 50HZ,SINGLE INPUT THERMOMETER W/USB RECORDING (INTL VERSION)
Fluke 54 II B	Dual Input Thermometer, 60Hz	TL	970	FLUKE-54-2 B 60HZ	FLUKE-54-2 B 60HZ,DUAL INPUT THERMOMETER W/ USB RECORDING, 60HZ NOISE REJECTION
Fluke 54 II B	Dual Input Thermometer, 50Hz	TL	970	FLUKE-54-2 B 50HZ	FLUKE-54-2 B 50HZ,DUAL INPUT THERMOMETER W/USB RECORDING (INTL VERSION)
Fluke 61	Infrared Thermometer	TL	368	FLUKE-61	FLUKE-61,IR THERMOMETER

Model	Açıklama	Para Birimi	Tavsiye edilen		Ürün Tanımı
			Son Kullanıcı	Parça numarı	
			Liste fiyatı		
Fluke 62 MAX	Infrared thermometer	TL	286	FLUKE-62 MAX	FLUKE-62 MAX,IP54 IR THERMOMETER
Fluke 62 MAX+	Infrared Thermometer	TL	341	FLUKE-62 MAX +	FLUKE-62 MAX +,IP54 IR THERMOMETER
Fluke 63	Infrared Thermometer	TL	830	FLUKE-63	FLUKE-63,INFRARED THERMOMETER TO 535C (999F)
Fluke 561	Multipurpose Thermometer	TL	467	FLUKE-561	FLUKE-561, IR THERMOMETER
Fluke 566	Multipurpose Thermometer	TL	1034	FLUKE-566	FLUKE-566,IR THERMOMETER
Fluke 568	Multipurpose Thermometer	TL	1372	FLUKE-568	FLUKE-568,IR THERMOMETER
Fluke 572	Precision IR Thermometer	TL	2392	FLUKE-572	FLUKE-572,PRECISION IR THERMOMETER
Fluke 572CF	Precision IR Thermometer (close focus option)	TL	2392	FLUKE-572-CF	FLUKE-572-CF,PRECISION IR THERMOMETER W/CLOSE FOCUS
Fluke 574	Precision IR Thermometer	TL	3556	FLUKE-574	FLUKE-574,PRECISION IR THERMOMETER W/LOGGING SW
Fluke 574CF	Precision IR Thermometer (close focus option)	TL	3556	FLUKE-574-CF	FLUKE-574-CF,PRECISION IR THERM W/LOGGING SW CLOSE FOCUS
Fluke FP	FoodPro Thermometer	TL	304	FLUKE-FP EU	FLUKE-FP EU,FOODPRO CELSIUS VERSION,EUR,ASIA,AMPAC
Fluke FP	Foodpro, food safety thermometer	TL	304	FLUKE-FP	FLUKE-FP,FOODPRO FOOD SAFETY THERMOMETER
Fluke FP Plus	FoodPro Plus Thermometer	TL	581	FLUKE-FP PLUS	FLUKE-FP PLUS,FOODPRO PLUS FOOD SAFETY THERMOMETER
Fluke T5-600/62MAX+/1A C kit	Electrical Tester, IR Thermometer and Voltage Detector Kit	TL	602	T5-600/62MAX+/1ACE	T5-600/62MAX+/1ACE,KIT WITH T5-600, 62MAX+, 1AC II, EUROPE VERSION
AN5	Analog Data Cable (574, 576)	TL	208	AN5	AN5,CABLE, ANALOG OUTPUT 1.5 M (5F) FOR FLUKE-57X SERIES
C50	Soft Meter Case	TL	91	C50	C50,CARRYING CASE
H6	Infrared Thermometer Holster (Fluke 63/65/68/561)	TL	107	H6	H6, IR-PISTOL-HOLSTER
80PR-60	RTD Temperature Probe (Fluke 66/68)	TL	204	80PR-60	80PR-60, IR-PISTOL-RTD PROBE

Görüntülü Termometreler

Fluke VT02	Visual IR Thermometer	TL	2456	FLK-VT02	FLK-VT02, 8HZ-VISUAL IR THERMOMETER, GLOBAL
------------	-----------------------	----	------	----------	---------------------------------------------

Termal Görüntüleme Cihazları

Termal Görüntüleme - Endüstriyel / Elektriksel

Fluke Ti29	Thermal Imager	TL	19197	FLK-TI29 9HZ	FLK-TI29 9HZ,INDUSTRIAL-COMMERCIAL THERMAL IMAGER, 9HZ
Fluke Ti27	Thermal Imager	TL	16636	FLK-TI27 9HZ	FLK-TI27 9HZ,INDUSTRIAL-COMMERCIAL THERMAL IMAGER, 9HZ

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke Ti32	Thermal Imager IR FlexCam	TL	22630	FLK-TI32 9HZ	FLK-TI32 9HZ, INDUSTRIAL-COMMERCIAL THERMAL IMAGER, 9HZ
Fluke Ti55FT- 20/7.5	Thermal Imager (IR- Fusion, 600°C, 20 mm), 7.5 Hz IR FlexCam	TL	56328	FLK-TI55FT- 20/7.5	FLK-TI55FT-20/7.5,IR FLX7.5HZ THERM IMAGR,320DLX F/W,FUSION20MM INT
Fluke Ti50FT- 20/7.5	Thermal Imager (IR- Fusion, 350°C, 20 mm), 7.5 Hz IR FlexCam	TL	47362	FLK-TI50FT- 20/7.5	FLK-TI50FT-20/7.5,IR FLX7.5HZ THERM IMAGR,320,S F/W,FUSION,20MM INT
Fluke Ti100	General Use Thermal Imager	TL	6390	FLK-TI100 9HZ	FLK-TI100 9HZ,GENERAL PURPOSE THERMAL IMAGER 9HZ
Fluke Ti105	Thermal Imager	TL	7673	FLK-TI105 9HZ	FLK-TI105 9HZ,INDUSTRIAL-COMMERCIAL THERMAL IMAGER 9HZ
Fluke Ti110	Industrial- Commercial Thermal Imager	TL	11513	FLK-TI110 9HZ	FLK-TI110 9HZ,INDUSTRIAL-COMMERCIAL THERMAL IMAGER 9HZ
Fluke Ti125	Industrial- Commercial Thermal Imager	TL	14074	FLK-TI125 9HZ	FLK-TI125 9HZ,INDUSTRIAL-COMMERCIAL THERMAL IMAGER 9HZ

Termal Görüntüleme - Özel Modeller

Fluke Ti50FT10/20/7.5	IR FlexCam Thermal Imager (IR- Fusion, 350°C, 10.5/20 mm), 7.5 Hz	TL	55918	FLK- TI50FT10/20/ 7.5	FLK-TI50FT10/20/7.5,IR FLX7.5HZ THERM IMAGR,320S F/W,FUSN10.5/20MM INT
Fluke Ti50FT20/54/7.5	IR FlexCam Thermal Imager (IR- Fusion, 350°C, 20/54 mm), 7.5 Hz	TL	60938	FLK- TI50FT20/54/ 7.5	FLK-TI50FT20/54/7.5,IR FLX7.5HZ THERM IMAGR,320S F/W,FUSION20/54MMINT
Fluke Ti50FT- 3L/7.5	IR FlexCam Thermal Imager (IR- Fusion, 350°C, 10.5/20/54 mm), 7.5 Hz	TL	69494	FLK-TI50FT- 3L/7.5	FLK-TI50FT-3L/7.5,IR FLX7.5HZ THERM IMAGR,320SF/WFUSN10.5/20/54MMINT
Fluke Ti55FT10/20/7.5	IR FlexCam Thermal Imager (IR- Fusion, 600°C, 10.5/20 mm), 7.5 Hz	TL	64883	FLK- TI55FT10/20/ 7.5	FLK-TI55FT10/20/7.5,IR FLX7.5HZ THERM IMAGR,320DF/W,FUSN10.5/20MM INT
Fluke Ti55FT20/54/7.5	IR FlexCam Thermal Imager (IR- Fusion, 600°C, 20/54 mm), 7.5 Hz	TL	69903	FLK- TI55FT20/54/ 7.5	FLK-TI55FT20/54/7.5,IR FLX7.5HZ THERM IMAGR,320,D F/W,FUSN20/54MM INT
Fluke Ti55FT- 3L/7.5	IR FlexCam Thermal Imager (IR- Fusion, 600°C, 10.5/20/54 mm), 7.5 Hz	TL	78459	FLK-TI55FT- 3L/7.5	FLK-TI55FT-3L/7.5,IR FLX7.5HZ THERM IMAGR,32DF/WFUSN10.5/20/54MMINT

Termal Görüntüleme - Bina Diagnostigi

Fluke TiR27	Thermal Imager	TL	16636	FLK-TIR27 9HZ	FLK-TIR27 9HZ,BUILDING DIAGNOSTICS THERMAL IMAGER, 9HZ
Fluke TiR29	Thermal Imager	TL	19197	FLK-TIR29 9HZ	FLK-TIR29 9HZ,BUILDING DIAGNOSTICS THERMAL IMAGER, 9HZ
Fluke TiR32	Thermal Imager	TL	22630	FLK-TIR32 9HZ	FLK-TIR32 9HZ, BUILDING DIAGNOSTICS THERMAL IMAGER, 9HZ

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke TiR3/FT-20/7.5	IR FlexCam Thermal Imager (IR-Fusion, 20 mm), 7.5 Hz	TL	30724	FLK-TIR3/FT-20/7.5	FLK-TIR3/FT-20/7.5,IR FLX7.5HZ BD THERM IMAGER,320,RAD,FUSN20MM INT
Fluke TIR3FT10/20/7.5	IR FlexCam Thermal Imager (IR-Fusion, 10.5/20 mm), 7.5 Hz	TL	39280	FLK-TIR3FT10/20/7.5	FLK-TIR3FT10/20/7.5,IR FLEXCAM THERMAL IMAGER W/FUSION,10.5/20MM, 7.5HZ
Fluke TIR4FT-10/20/7.5	IR FlexCam Thermal Imager (IR-Fusion, 10.5/20 mm), 7.5 Hz	TL	48245	FLK-TIR4FT-10/20/7.5	FLK-TIR4FT-10/20/7.5,IR FLEXCAM THERMAL IMAGER,FUSN,10.5/20MM, 7.5HZ
Fluke TiR4/FT-20/7.5	IR FlexCam Thermal Imager (IR-Fusion, 20 mm), 7.5 Hz	TL	39689	FLK-TIR4/FT-20/7.5	FLK-TIR4/FT-20/7.5,IR FLX7.5HZ BD THERM IMAGER,320 DRAD,FUSN20MM INT
Fluke Ti100	General Use Thermal Imager	TL	6390	FLK-TI100	FLK-TI100 9HZ,GENERAL PURPOSE THERMAL IMAGER 9HZ
Fluke TiR105	Thermal Imager	TL	7673	FLK-TIR105	FLK-TIR105 9HZ,BUILDING DIAGNOSTICS THERMAL IMAGER 9HZ
Fluke TiR110	Building Diagnostics Thermal Imager	TL	11513	FLK-TIR110	FLK-TIR110 9HZ,BUILDING DIAGNOSTICS THERMAL IMAGER 9HZ
Fluke TiR125	Building Diagnostics Thermal Imager	TL	14074	FLK-TIR125	FLK-TIR125 9HZ,,BUILDING DIAGNOSTICS THERMAL IMAGER 9HZ

Termal Görüntüleme Aksesuarları

TI-CAR CHARGER	Ti Car Charger (TiR/TiR1/Ti10/Ti20/Ti25)	TL	281	TI-CAR CHARGER	TI-CAR CHARGER,CAR CHARGER FOR TIR/TIR1/TI10/TI20/TI25
TI-VISOR	Sun Visor	TL	192	TI-VISOR	TI-VISOR,VISOR FOR TI10/TI25/TIR/TIR1
Fluke TI-Visor2	Sun Visor	TL	192	FLK-TI-VISOR2	FLK-TI-VISOR2,VISOR FOR TI100, TI110, TI125, TIR110, AND TIR125
Ti20-RBP	Rechargeable Battery Pack (Ti20)	TL	398	TI20-RBP	TI20-RBP,RECHARGEABLE BATTERY PACK
Ti-SBC	Battery Charger (IR FlexCam)	TL	1178	FLK-TI-SBC	FLK-TI-SBC,104465,IR SMART BATTERY CHARGER
TI-TRIPOD	Tripod Mounting Base	TL	256	TI-TRIPOD	TI-TRIPOD,TRIPOD MOUNTING ACCESSORY/HOLDER
Fluke-TI-Tripod2	Mounting Base	TL	256	FLK-TI-TRIPOD2	FLK-TI-TRIPOD2,TRIPOD MTG ACCESSORY/HOLDER, TI100-110-125
FLK-TI-SBC3	Charging base (Ti32/TiR32)	TL	448	FLK-TI-SBC3	FLK-TI-SBC3,SMART BATTERY CHARGER 3
FLK-TI-SBP3	Extra battery (Ti32/TiR32)	TL	320	FLK-TI-SBP3	FLK-TI-SBP3,SMART BATTERY PACK 3
FLK-LENS/TELE1	Telephoto Infrared Lens (Ti32/TiR32)	TL	2548	FLK-LENS/TELE1	FLK-LENS/TELE1,INFRARED TELEPHOTO LENS 1
FLK-LENS/WIDE1	Wide-angle Infrared Lens (Ti32/TiR32)	TL	2548	FLK-LENS/WIDE1	FLK-LENS/WIDE1,INFRARED WIDE-ANGLE LENS 1
Car charger	Car charger (IR FlexCam)	TL	487	104543	104543,VEHICLE ADAPTER, BATTERY CHARGER, FLEXCAM

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
-------	----------	-------------	-------------------------------------------------	--------------	-------------

Termal Görüntüleme IR- Pencere

FLK-050-CLKT	Fluke-050-CLKT	TL	766	FLK-050-CLKT	FLK-050-CLKT,2 IN (50MM) C-RANGE IR WINDOW, KWIK TWIST
FLK-075-CLKT	Fluke-075-CLKT	TL	1022	FLK-075-CLKT	FLK-075-CLKT,3 IN (75MM) C-RANGE IR WINDOW, KWIK TWIST
FLK-100-CLKT	Fluke-100-CLKT	TL	1601	FLK-100-CLKT	FLK-100-CLKT,4 IN (100MM) C-RANGE IR WINDOW, KWIK TWIST
FLK-075-CLKTO	Fluke-075-CLKTO	TL	897	FLK-075-CLKTO	FLK-075-CLKTO,3 IN (75MM) C-RANGE,INDOOR MEDIUM VOLTAGE,IR WINDOW,KWIK TWIST

ScopeMeter Cihazları

Endüstriyel ScopeMeter

Fluke 123	Industrial ScopeMeter (20 MHz)	TL	3774	FLUKE-123/001	FLUKE-123/001, INDUSTRIAL SCOPEMETER 20MHZ, CENTRAL EU
Fluke 123	Industrial ScopeMeter (20 MHz)	TL	3906	FLUKE-123/008	FLUKE-123/008, INDUSTRIAL SCOPEMETER 20MHZ, UNIVERSAL INT.
Fluke 123/S	Industrial ScopeMeter (20 MHz) + SCC120	TL	4661	FLUKE-123/001S	FLUKE-123/001S, INDUSTRIAL SCOPEMETER 20MHZ, CENTRAL EU
Fluke 123/S	Industrial ScopeMeter (20 MHz) + SCC120	TL	4787	FLUKE-123/008S	FLUKE-123/008S, INDUSTRIAL SCOPEMETER 20MHZ, UNIVERSAL INT.
Fluke 124	Industrial ScopeMeter (40 MHz)	TL	4661	FLUKE-124/001	FLUKE-124/001, INDUSTRIAL SCOPEMETER 40MHZ, CENTRAL EU
Fluke 124/S	Industrial ScopeMeter (40 MHz) + SCC120	TL	5429	FLUKE-124/001S	FLUKE-124/001S, INDUSTRIAL SCOPEMETER 40MHZ, CENTRAL EU
Fluke 124/S	Industrial ScopeMeter (40 MHz) + SCC120	TL	5571	FLUKE-124/008S	FLUKE-124/008S, INDUSTRIAL SCOPEMETER 40MHZ, UNIVERSAL INT.
Fluke 125	Industrial ScopeMeter (40 MHz)	TL	5562	FLUKE-125/001	FLUKE-125/001,40MHZ INDUSTR.SCOPEMETER,CENTRAL EU
Fluke 125	Industrial ScopeMeter (40 MHz) + SCC120	TL	5697	FLUKE-125/008	FLUKE-125/008,40MHZ INDUSTR.SCOPEMETER,UNIVERSAL/INT.
Fluke 125/S	Industrial ScopeMeter (40 MHz) + SCC120	TL	6479	FLUKE-125/001S	FLUKE-125/001S,40MHZ INDUSTR.SCOPEM+SCC,CENTRAL EU
Fluke 125/S	Industrial ScopeMeter (40 MHz) + SCC120	TL	6614	FLUKE-125/008S	FLUKE-125/008S,40MHZ INDUSTR.SCOPEM+SCC,UNIVERSAL/INT.

190 Serisi ScopeMeter Cihazları

Fluke 190-204/EU	ScopeMeter 4 Channel 200 MHz Color	TL	11117	FLUKE-190-204/EU	FLUKE-190-204/EU,SCOPEMETER 4 CHANNEL 200 MHZ COLOR EU
Fluke 190-204/UN	ScopeMeter 4 Channel 200 MHz Color	TL	11117	FLUKE-190-204/UN	FLUKE-190-204/UN,SCOPEMETER 4 CHANNEL 200 MHZ COLOR UNI

Model	Açıklama	Para Birimi	Tavsiye edilen		
			Son Kullanıcı	Parça numarı: Ürün Tanımı	
			Liste fiyatı		
Fluke 190-204/EU/S	ScopeMeter 4 Channel 200 MHZ Color Uni SCC	TL	12160	FLUKE-190-204/EU/S	FLUKE-190-204/EU/S,SCOPEMETER 4 CHANNEL 200 MHZ COLOR EU SCC
Fluke 190-204/UN/S	ScopeMeter 4 Channel 200 MHZ Color UNI SCC	TL	12160	FLUKE-190-204/UN/S	FLUKE-190-204/UN/S,SCOPEMETER 4 CHANNEL 200 MHZ COLOR UNI SCC
Fluke 190-104/UN	ScopeMeter 4 Channel 100 MHZ Color UNI	TL	9807	FLUKE-190-104/UN	FLUKE-190-104/UN,SCOPEMETER 4 CHANNEL 100 MHZ COLOR UNI
Fluke 190-104/EU	ScopeMeter 4 Channel 100 MHZ Color EU	TL	9807	FLUKE-190-104/EU	FLUKE-190-104/EU,SCOPEMETER 4 CHANNEL 100 MHZ COLOR EU
Fluke 190-104/EU/S	ScopeMeter 4 Channel 100 MHZ Color EU SCC	TL	10859	FLUKE-190-104/EU/S	FLUKE-190-104/EU/S,SCOPEMETER 4 CHANNEL 100 MHZ COLOR EU SCC
Fluke 190-104/UN/S	ScopeMeter 4 Channel 100 MHZ Color UNI SCC	TL	10859	FLUKE-190-104/UN/S	FLUKE-190-104/UN/S,SCOPEMETER 4 CHANNEL 100 MHZ COLOR UNI SCC
Fluke 190-062/EU	ScopeMeter 2 Channel 60 MHZ Color	TL	7570	FLUKE-190-062/EU	FLUKE-190-062/EU,SCOPEMETER 2CH 60MHZ COL EU
Fluke 190-062/UN	ScopeMeter 2 Channel 60MHZ Color	TL	7570	FLUKE-190-062/UN	FLUKE-190-062/UN,SCOPEMETER 2CH 60MHZ COL UNI
Fluke 190-062/EU/S	ScopeMeter 2 Channel Color SCC	TL	8615	FLUKE-190-062/EU/S	FLUKE-190-062/EU/S,SCOPEMETER 2CH 60MHZ COL EU SCC
Fluke 190-062/UN/S	ScopeMeter 2 Channel 60MHZ Color SCC	TL	8615	FLUKE-190-062/UN/S	FLUKE-190-062/UN/S,SCOPEMETER 2CH 60MHZ COL UNI SCC
Fluke 190-102/EU	ScopeMeter 2 Channel 100MHZ Color	TL	8709	FLUKE-190-102/EU	FLUKE-190-102/EU,SCOPEMETER 2CH 100MHZ COL EUROPE
Fluke 190-102/UN	ScopeMeter 2 Channel 100MHZ Color SCC	TL	8709	FLUKE-190-102/UN	FLUKE-190-102/UN,SCOPEMETER 2CH 100MHZ COL UNIVERSAL
Fluke 190-102/EU/S	ScopeMeter 2 Channel 100MHZ Color SCC	TL	9757	FLUKE-190-102/EU/S	FLUKE-190-102/EU/S,SCOPEMETER 2CH 100MHZ COL EUROPE SCC
Fluke 190-102/UN/S	ScopeMeter 2 Channel 100MHZ Color SCC	TL	9757	FLUKE-190-102/UN/S	FLUKE-190-102/UN/S,SCOPEMETER 2CH 100MHZ COL UNIVERS SCC
Fluke 190-202/EU	ScopeMeter 2 Channel 200MHZ Color	TL	9651	FLUKE-190-202/EU	FLUKE-190-202/EU,SCOPEMETER 2CH 200MHZ COL EUROPE
Fluke 190-202/UN	ScopeMeter 2 Channel 200MHZ Color	TL	9651	FLUKE-190-202/UN	FLUKE-190-202/UN,SCOPEMETER 2CH 200MHZ COL UNIVERSAL
Fluke 190-202/EU/S	ScopeMeter 2 Channel 200MHZ Color SCC	TL	10696	FLUKE-190-202/EU/S	FLUKE-190-202/EU/S,SCOPEMETER 2CH 200MHZ COL EUROPE SCC
Fluke 190-202/UN/S	ScopeMeter 2 Channel 200MHZ Color SCC	TL	10696	FLUKE-190-202/UN/S	FLUKE-190-202/UN/S,SCOPEMETER 2CH 200MHZ COL UNIVERS SCC
Fluke 190-502/EU	ScopeMeter 2 Channel 500 MHZ Color	TL	12014	FLUKE-190-502/EU	FLUKE-190-502/EU,SCOPEMETER 2CH 500MHZ COL EUROPE
Fluke 190-502/UN	ScopeMeter 2 Channel 500 MHZColor UNI	TL	12014	FLUKE-190-502/UN	FLUKE-190-502/UN,SCOPEMETER 2CH 500MHZ COL UNIVERSAL
Fluke 190-502/EU/S	ScopeMeter 2 Channel 500 MHZ Color Europe SCC	TL	13036	FLUKE-190-502/EU/S	FLUKE-190-502/EU/S,SCOPEMETER 2CH 500MHZ COL EUROPE SCC
Fluke-190-502/UN/S	ScopeMeter 2 Channel 500 MHZ Color UNI SCC	TL	13036	FLUKE-190-502/UN/S	FLUKE-190-502/UN/S,SCOPEMETER 2CH 500MHZ COL UNIVERS SCC

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
ScopeMeter Aksesuarları					
AC120	Heavy Duty Alligator Clips	TL	87	AC120	AC120,ALLIGATOR CLIP-SET
BB120	Banana to BNC Adapter Plug	TL	89	BB120	BB120,SET OF 2 BANANA TO BNC ADAPTOR
BC190/801	Battery Charger/Line Voltage Adapter EUR (190 Series)	TL	256	BC190/801	BC190/801,BATTERY CHARGER, EURO
BC190/808	Battery Charger/Line Voltage Adapter UNIVERSAL (190 Series)	TL	306	BC190/808	BC190/808,BATTERY CHARGER, UNIVERSAL
BHT190	Set of Break-out Adapters	TL	1246	BHT190	BHT190,BUS HEALTH TEST ADAPTER, DB-9 AND M-12
BP120MH	NiMH Battery Pack (120 Series/43B)	TL	256	BP120MH	BP120MH,RECHARGEABLE BATTERY PACK FOR 43, 43B & 123
BP190	NiMH Battery Pack (190 Series)	TL	393	BP190	BP190,NIMH BATTERY PACK
C120	Hard Case (43B/120 Series)	TL	274	C120	C120,HARD CARRYING CASE FOR 120 SERIES
C125	Soft Meter Case	TL	101	C125	C125,COMPACT SOFT CASE 120 SERIES
C190	Hard Case (190 Series)	TL	446	C190	C190,HARDCASE SM 190 SERIES
C195	Soft Case	TL	423	C195	C195,SOFTCASE
CS20MA	Current Shunt 4-20 mA	TL	215	CS20MA	CS20MA,CURRENT SHUNT 4-20MA
DP120	Differential Probe	TL	1553	DP120	DP120,DIFFERENTIAL PROBE
HC120	Hook Clips	TL	105	HC120	HC120,SET OF 2 HOOK CLIPS
HC200	Hook Clips	TL	94	HC200	HC200,HOOK CLIP SET, 2 RED 2 GRAY
ITP120	Trigger Probe	TL	830	ITP120	ITP120,ISOLATED TRIGGER PROBE
MA190	Medical Accessory Kit (190 Series)	TL	917	MA190	MA190,SCMTR MEDICAL ACC KIT
OC4USB	Serial Interface Adapter/Cable (USB)	TL	462	OC4USB	OC4USB,USB CABLE FOR SCOPEMETER 12X,19X,PQA,43X
PM8907/801	Battery Charger/Line Voltage Adapter EUR (120 Series)	TL	220	PM8907/801	PM8907/801,POWER ADAPTOR/BATTERY CHARGER-EUROPE
PM8907/808	Battery Charger/Line Voltage Adapter UNIVERSAL (120 Series)	TL	256	PM8907/808	PM8907/808,POWER ADAPTOR/BATT CHARGER-UNIVERSAL
PM9080	Serial Interface Adapter/Cable (RS232)	TL	485	PM9080/101	PM9080/101,OPTICAL TO RS232 INTERFACE ADAPTER
PM9081	Dual Banana Plug to Female BNC Adapter	TL	114	PM9081/001	PM9081/001,DUAL BANANA PLUG TO FEM. BNC ADAPTER
PM9082	Dual Banana Jack to Male BNC Adapter	TL	114	PM9082/001	PM9082/001,BANANA JACK TO MALE BNC ADAPTER
PM9091	Coaxial BNC Cables (1.5 m)	TL	220	PM9091/001	PM9091/001,1.5M (5FT) SAFETY DESIGNED COAX CABLE
PM9092	Coaxial BNC Cables (0.5 m)	TL	194	PM9092/001	PM9092/001,0.5M (1.5FT) SFTY DESIGNED COAX CABLE

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
PM9093	Male BNC to Female BNC Adapter	TL	135	PM9093/001	PM9093/001,SAFETY DESIGNED BNC T- CONNECTOR
PM9096/201	Secondary Pick-up	TL	755	PM9096/201	PM9096/201,SECONDARY PICK UP 1000:1
SCC120E	FlukeView Software + USB Cable + Case (120 Series) - English	TL	940	SCC120E	SCC120E,SOFTWARE & CABLE CARR.CASE120 SERIES
SCC128	Automotive Accessory Kit (120 Series)	TL	1921	SCC 128	SCC 128,AUTOMOTIVE ACC KIT 120 SERIES
SCC198	Automotive Accessory Kit (190 Series)	TL	2237	SCC 198	SCC 198,AUTOMOTIVE ACC KIT 190 SERIES
SCC190	FlukeView Software + Cable + Case (190 Series) - English, French, German	TL	1349	SCC190EFG	SCC190EFG,SW & CABLE CARRYING CASE
STL90	Automotive Shielded Test Lead Set (120/190 Series)	TL	533	STL90	STL90,SHIELDED TESTLEAD SET - STL90
TAS90	Automotive Accessory Set (120/190 Series)	TL	174	TAS90	TAS90,SHIELDED TEST LEAD ACC. SET
VPS101	1:1 Voltage Probe Set, black, 30 MHz, 1.2m	TL	503	VPS101	VPS101,1:1 VOLTAGE PROBE SET,BLACK,30 MHZ,1.2M
VPS210-G	10:1 Voltage Probe Set, grey, 200 MHz, 1.2m	TL	503	VPS210-G	VPS210-G,10:1 VOLTAGE PROBE SET, GREY, 200 MHZ, 1.2M,
VPS210-R	10:1 Voltage Probe Set, 1 red, 200 MHz, 1.2m	TL	503	VPS210-R	VPS210-R,10:1 VOLTAGE PROBE SET, RED, 200 MHZ, 1.2M,
VPS212-G	10:1 Voltage Probe Set, grey, 200 MHz, 2.5m	TL	503	VPS212-G	VPS212-G,10:1 VOLTAGE PROBE SET,GREY,200 MHZ,2.5M
VPS212-R	10:1 Voltage Probe Set, red, 200 MHz, 2.5m	TL	503	VPS212-R	VPS212-R,10:1 VOLTAGE PROBE SET,RED,200 MHZ,2.5M
VPS220-G	100:1 Voltage Probe Set, grey, 200 MHz, 1.2m	TL	503	VPS220-G	VPS220-G,100:1 VOLTAGE PROBE SET,GREY,200 MHZ,1.2M
VPS220-R	100:1 Voltage Probe Set, red, 200 MHz, 1.2m	TL	503	VPS220-R	VPS220-R,100:1 VOLTAGE PROBE SET,RED,200 MHZ,1.2M
BP291	Battery Pack, Fluke 190 Series	TL	784	BP291	BP291,LI-ION BATTERY PACK, DOUBLE CAPACITY, FLUKE 190-SERIESII
VPS410-R	Voltage Probe Set 10:1 Red	TL	494	VPS410-R	VPS410-R,VOLTAGE PROBE SET 10:1, RED
VPS410-B	Voltage Probe Set 10:1 Blue	TL	494	VPS410-B	VPS410-B,VOLTAGE PROBE SET 10:1, BLUE
VPS410-G	Voltage Probe Set 10:1 Grey	TL	494	VPS410-G	VPS410-G,VOLTAGE PROBE SET 10:1, GREY
VPS410-V	Voltage Probe Set 10:1 Green	TL	494	VPS410-V	VPS410-V,VOLTAGE PROBE SET 10:1, GREEN
C290	Hard-Shell Carrying Case	TL	526	C290	C290,HARD-SHELL CARRYING CASE
SCC290	Software and Carrying Case Kit	TL	1084	SCC290	SCC290,SOFTWARE, CARRYING CASE KIT

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
AS400	Probe Extension Set, for VPS400 Probes	TL	284	AS400	AS400,PROBE ACCESSORY SET, FOR VPS400 PROBES
RS400	Probe Replacement Set, for VPS400 Probes	TL	375	RS400	RS400,PROBE ACCESSORY REPLACEMENT SET, FOR VPS400 PROBES
BP290 Battery Pack	Battery Pack Single Cap 190-series II	TL	604	BP290	BP290,LI-ION BATT PACK SINGLE CAP 190-SERIESII
HH290 Hanging Hook	Hanging Hook, ScopeMeter Series 190 II	TL	206	HH290	HH290,HANGING HOOK, SCOPEMETER 190-SERIESII
STL120-III	Shielded Test Lead	TL	322	STL120-III	STL120-III,SHIELDED TEST LEAD SET, 12.5MHZ,1.2M
VPS40-III	Voltage Probe	TL	368	VPS40-III	VPS40-III,VOLTAGE PROBE 10:1 40 MHZ BLACK, 1.2M
RS120-III	Probe Accessory Replacement Set	TL	245	RS120-III	RS120-III,REPLACEMENT ACCESSORIES FOR STL120-III
VPS420-R	High Working Voltage Probe 100:1 Red & Black	TL	640	VPS420-R	VPS420-R,VOLTAGE PROBE SET 150 MHZ 100:1, 2000V (1000V CAT III TO EARTH)
PM8907/807	POWER ADAPTOR/BATTERY CHARGER	TL	220	PM8907/807	PM8907/807,POWER ADAPTOR/BATTERY CHARGER
VPS510-R	Voltage Probe set 500 MHZ 10:1 Red	TL	499	VPS510-R	VPS510-R,VOLT.PROBE SET 500MHZ 10:1 RED
VPS510-B	Voltage probe set 500 MHZ 10:1 Blue	TL	499	VPS510-B	VPS510-B,VOLT.PROBE SET 500MHZ 10:1 BLUE
VPS510-G	Voltage probe set 500 MHZ 10:1 Grey	TL	499	VPS510-G	VPS510-G,VOLT.PROBE SET 500MHZ 10:1 GRAY
VPS510-V	Voltage probe set 500 MHZ 10:1 Green	TL	499	VPS510-V	VPS510-V,VOLT.PROBE SET 500MHZ 10:1 GREEN
TRM50	50 Ohm feed-through terminator BNC	TL	499	TRM50	TRM50,50 OHM FEED-THROUGH TERMINATOR BNC
RS500	Probe accessory replacement set for VPS500 probes	TL	421	RS500	RS500,PROBE ACCESS.REPL.SET FOR VPS500 PROBES
FlukeView Software	FlukeView Software	TL	675	SW90W	SW90W,FLUKEVIEW SCOPEMETER

Güç Kalitesi Cihazları

Fluke 43Basic	Power Quality Analyzer (single-phase)	TL	5365	FLUKE-43BASIC/001	FLUKE-43BASIC/001, POWER QUALITY ANALYZER BASIC VERSION, EURO
Fluke 43B/001	Power Quality Analyzer (single-phase) / euro	TL	8105	FLUKE-43B/001	FLUKE-43B/001,POWER QUALITY ANALYZER,EURO

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke 43B	Power Quality Analyzer (single-phase)	TL	8105	FLUKE-43B/003	FLUKE-43B/003,POWER QUALITY ANALYZER, USA
Fluke 43B/008	Power Quality Analyzer (single-phase) -universal	TL	8734	FLUKE-43B/008	FLUKE-43B/008,POWER QUALITY ANALYZER,UNIVERSAL
Fluke 43B	Power Quality Analyzer (single-phase)	TL	8105	FLUKE-43B/101	FLUKE-43B/101,POWER QUALITY ANALYZER,FINLAND
Fluke 345	Power Quality Clamp Meter	TL	6001	FLUKE-345	FLUKE-345,POWER QUALITY CLAMP METER
Fluke 434/LOG	Upgrade kit for Fluke 434	TL	4650	FLUKE-434/LOG	FLUKE-434/LOG, FIRMWARE/SOFTWARE UPGRADE FOR FLUKE-434
Fluke 434-II	Power Quality and energy analyzer	TL	14450	FLUKE-434-II	FLUKE-434-II,PQ AND ENERGY ANALYZER
Fluke 434-II/BASIC	Power Quality and energy analyzer (w/o clamps)	TL	12501	FLUKE-434-II/BASIC	FLUKE-434-II/BASIC,PQ AND ENERGY ANALYZER (W/O CLAMPS)
Fluke 435-II	Advanced Power Quality and energy analyzer	TL	18022	FLUKE-435-II	FLUKE-435-II,ADVANCED PQ AND ENERGY ANALYZER
Fluke 435-II/BASIC	Advanced Power Quality and energy analyzer (w/o clamps)	TL	16073	FLUKE-435-II/BASIC	FLUKE-435-II/BASIC,ADVANCED PQ AND ENERGY ANALYZER (W/O CLAMPS)
Fluke 437-II	400 Hz Power Quality and Energy Analyzer	TL	24515	FLUKE-437-II	FLUKE-437-II,400HZ POWER QUALITY AND ENERGY ANALYZER
Fluke 437-II/BASIC	400 Hz Power Quality and Energy Analyzer (w/o clamps)	TL	22566	FLUKE-437-II/BASIC	FLUKE-437-II/BASIC,400HZ POWER QUALITY AND ENERGY ANALYZER (W/O CLAMPS)
Fluke 1735	Power Logger (three-phase)	TL	8334	FLUKE-1735	FLUKE-1735,POWER LOGGER - ANALYST
Fluke 1743 Basic	Power Quality Logger, Memobox	TL	10488	FLUKE-1743 BASIC	FLUKE-1743 BASIC,POWER QUALITY LOGGER (WITHOUT PROBES)
Fluke 1743	Power Quality Logger, Memobox	TL	12538	FLUKE-1743	FLUKE-1743,POWER QUALITY LOGGER - MEMOBOX
Fluke 1744 Basic	Power Quality Logger, Memobox	TL	13704	FLUKE-1744 BASIC	FLUKE-1744 BASIC,POWER QUALITY LOGGER (WITHOUT PROBES)
Fluke 1744	Power Quality Logger, Memobox	TL	15751	FLUKE-1744	FLUKE-1744,POWER QUALITY LOGGER - MEMOBOX
Fluke 1744/1PH	Power Quality Logger, Memobox	TL	5631	FLUKE-1744/1PH	FLUKE-1744/1PH,POWER QUALITY LOGGER, 1 PHASE
Fluke 1745	Power Quality Logger, Memobox	TL	18964	FLUKE-1745	FLUKE-1745,POWER QUALITY LOGGER - MEMOBOX
Fluke 1750/B	Basic Power Recorder	TL	30912	FLUKE-1750/B	FLUKE-1750/B,BASIC POWER RECORDER
Fluke 1750	Power Recorder	TL	34301	FLUKE-1750	FLUKE-1750,POWER RECORDER
Fluke 1760 Basic	Power Quality Recorder (three-phase), Topas	TL	40956	FLUKE-1760 BASIC	FLUKE-1760 BASIC,POWER QUALITY RECORDER-TOPAS,W/O V OR I PROBES,NO TRANS
Fluke 1760	Power Quality Recorder (three-phase), Topas	TL	47028	FLUKE-1760 INTL	FLUKE-1760 INTL,POWER QUALITY RECORDER - TOPAS,CONFIGURED INTL RANGE,NO TRANS
Fluke 1760TR Basic	Power Quality Recorder (three-phase), Topas	TL	57652	FLUKE-1760TR BASIC	FLUKE-1760TR BASIC,POWER QUALITY RECORDER W/TRANS - TOPAS,W/O V OR I PROBES
Fluke 1760TR	Power Quality Recorder (three-phase), Topas	TL	63724	FLUKE-1760 TR INTL	FLUKE-1760 TR INTL,POWER QUALITY RECORDER W/TRANS-TOPAS,CONFIGURED INTL RANGE

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
-------	----------	-------------	-------------------------------------------------	--------------	-------------

Fluke VR1710	Single-Phase Voltage Quality Recorder	TL	2383	FLUKE-VR1710	FLUKE-VR1710,VOLTAGE QUALITY RECORDER
C1740	Softcase for 174X and 43X-II PQ analyzer	TL	567	C1740	C1740,SOFTCASE FOR 174X AND 43X-II PQ ANALYZER
C437-II	Hard case 430 Series II with rollers	TL	1397	C437-II	C437-II,HARD CASE 430 SERIES II WITH ROLLERS

Güç Kalitesi Cihazları Aksesuarları

BC430	Battery Charger/Line Voltage Adapter	TL	407	BC430	BC430,BATTERY CHARGER 230V/110V
BE345	Battery Eliminator (Fluke 345)	TL	471	BE345	BE345,UNIVERSAL BATTERY ELIMINATOR FOR FLUKE-345
BP120MH	NiMH Battery Pack (120 Series/43B)	TL	256	BP120MH	BP120MH,RECHARGEABLE BATTERY PACK FOR 43, 43B & 123
CF1760-2GB	Compact Flash Card 2GB (Fluke 1760)	TL	1201	CF1760-2GB	CF1760-2GB,X76980200000,2GB COMPACT FLASH CARD
C120	Hard Case (43B/120 Series)	TL	274	C120	C120,HARD CARRYING CASE FOR 120 SERIES
C435	Hard Case with rollers (430 Series)	TL	1217	C435	C435,WATER-TIGHT HARD CASE W/ROLLERS
CS1750	Soft Case (Fluke 1750/1760)	TL	768	CS1750/1760	CS1750/1760,CASE POLYESTER, FOR FLUKE 1750 & 1760
CS1760	Crossover Ethernet Cable (Fluke 1760)	TL	73	CS1760	CS1760,X57320800100,CROSSOVER ETHERNET CABLE
GPS430	GPS Time Synchronization Module (430 Series)	TL	3442	GPS430	GPS430,GPS SYNC MODULE FOR FLUKE 430 SERIES
GPS-TIME SYNC	GPS Time Synchronization Module (Fluke 1760)	TL	1342	GPS-TIME SYNC	GPS-TIME SYNC,EP2050Z, OPTION GPS TIMESYNC FOR FLUKE-1760 AND TOPAS 2000
i1A/10A CLAMP PQ1	1-phase Mini Current Clamp Set	TL	1114	I1A/10A CLAMP PQ1	I1A/10A CLAMP PQ1,1-PHASE 1A/10A MINI CURRENT CLAMP SET FOR PQ
i1A/10A CLAMP PQ3	3-phase Mini Current Clamp Set	TL	1539	I1A/10A CLAMP PQ3	I1A/10A CLAMP PQ3,3-PHASE 1A/10A MINI CURRENT CLAMP SET FOR PQ
i1A/10A CLAMP PQ4	4-phase Mini Current Clamp Set	TL	2015	I1A/10A CLAMP PQ4	I1A/10A CLAMP PQ4,4-PHASE 1A/10A MINI CURRENT CLAMP SET FOR PQ
i5A/50A CLAMP PQ3	3-phase Mini Current Clamp Set	TL	1539	I5A/50A CLAMP PQ3	I5A/50A CLAMP PQ3,3-PHASE 5A/50A MINI CURRENT CLAMP SET FOR PQ
i5A/50A CLAMP PQ4	4-phase Mini Current Clamp Set	TL	2015	I5A/50A CLAMP PQ4	I5A/50A CLAMP PQ4,4-PHASE 5A/50A MINI CURRENT CLAMP SET FOR PQ

Model	Açıklama	Para Birimi	Tavsiye edilen		Ürün Tanımı
			Son Kullanıcı	Parça numar.	
			Liste fiyatı		
i5s	AC Current Clamp (5 A)	TL	1288	I5S	I5S,5A AC CURRENT PROBE
i5sPQ3	AC Current Clamp (5 A), 3-pack	TL	2957	I5SPQ3	I5SPQ3,5A AC CURRENT PROBE 3 PACK FOR 430
i20/200A CLAMP PQ3	3-phase Mini Current Clamp Set	TL	1539	I20/200A CLAMP PQ3	I20/200A CLAMP PQ3,3-PHASE 20A/200A MINI CURRENT CLAMP SET FOR PQ
i20/200A CLAMP PQ4	4-phase Mini Current Clamp Set	TL	2015	I20/200A CLAMP PQ4	I20/200A CLAMP PQ4,4-PHASE 20A/200A MINI CURRENT CLAMP SET FOR PQ
i400s	AC Current Clamp (400A)	TL	656	I400S	I400S,AC CURRENT CLAMP-ON PROBE
OC4USB	Serial Interface Adapter/Cable (USB)	TL	462	OC4USB	OC4USB,USB CABLE FOR SCOPEMETER 12X,19X,PQA,43X
PM9080	Serial Interface Adapter/Cable (RS232)	TL	485	PM9080/101	PM9080/101,OPTICAL TO RS232 INTERFACE ADAPTER
SW43W	FlukeView Software (Fluke 43B/430 Series)	TL	878	SW43W	SW43W,FLUKEVIEW 43 SOFTWARE
TLS430	Test Leads and Alligator Clips (4 black, 1 green) - 430 Series	TL	279	TLS430	TLS430,TEST LEAD SET 430
3140R	Clip-on Current Transformer 2A-400A (Fluke 1750)	TL	1379	3140R	3140R, CURRENT CLAMP, 400 AMP
TPS CLAMP 10A/1A	Clip-on Current Transformer 10A/1A (Fluke 1760)	TL	1185	TPS CLAMP 10A/1A	TPS CLAMP 10A/1A,A680501049, CURRENT PROBE 10/1A AC
TPS CLAMP 50A/5A	Clip-on Current Transformer 50A/5A (Fluke 1760)	TL	1185	TPS CLAMP 50A/5A	TPS CLAMP 50A/5A,A680501048, CURRENT PROBE 50A/5A AC
TPS CLAMP 200A/20A	Clip-on Current Transformer 200A/20A (Fluke 1760)	TL	1185	TPS CLAMP 200/20	TPS CLAMP 200/20,A680501050, CURRENT PROBE 200/20A AC
TPS SHUNT 20MA	Shunt 20mA AC/DC (Fluke 1760)	TL	1004	TPS SHUNT 20MA	TPS SHUNT 20MA,A680501057, SHUNT 20 MA AC/DC
TPS VOLTPROBE 10V	Voltage Probe 10V (Fluke 1760)	TL	958	TPS VOLTPROBE 10V	TPS VOLTPROBE 10V,EP2073A, VOLTAGE PROBE 10 V
TPS VOLTPROBE 100V	Voltage Probe 100V (Fluke 1760)	TL	958	TPS VOLTPROBE 100V	TPS VOLTPROBE 100V,EP2075A, VOLTAGE PROBE 100 V
TPS VOLTPROBE 400V	Voltage Probe 400V (Fluke 1760)	TL	958	TPS VOLTPROBE 400V	TPS VOLTPROBE 400V,EP2077A, VOLTAGE PROBE 400 V
TPS VOLTPROBE 600V	Voltage Probe 600V (Fluke 1760)	TL	958	TPS VOLTPROBE 600V	TPS VOLTPROBE 600V,EP2083A, VOLTAGE PROBE 600 V
TPS VOLTPROBE 1KV	Voltage Probe 1000V (Fluke 1760)	TL	1452	TPS VOLTPROBE 1K V	TPS VOLTPROBE 1K V,EP2085A, VOLTAGE PROBE 1000 V
FLUKE-1750/CASE	Hard Case (Fluke 1750)	TL	1656	FLUKE-1750/CASE	FLUKE-1750/CASE, TRANSIT CASE, MOLDED, FLK-1750 AND 1760
FLUKE-1750/SEAT-L	Fluke Power Analyze - Additional SEAT LICENSE	TL	3341	FLUKE-1750/SEAT-L	FLUKE-1750/SEAT-L,1 SEAT LICENSE FOR FLUKE-1750 PWR ANALYZER SOFTWARE

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
FLUKE-1750/SITE-L	Fluke Power Analyze - Additional SITE LICENCE	TL	16679	FLUKE-1750/SITE-L	FLUKE-1750/SITE-L,1 SITE LICENSE FOR FLUKE-1750 PWR ANALYZER SOFTWARE
WC100	Color Localization Set (430 Series)	TL	91	WC100	WC100,MULTI COLOR WIRE CLIPS
1743/1744 POLESET	Pole Mounting Kit (Fluke 1743/1744)	TL	135	1743/44	1743/44 POLESET,POLE MOUNTING KIT FOR 1743/44
3000/6000A-TF-4	4-Phase Flex Current Clamp Set	TL	4874	FS3000/6000 A-TF-4	FS3000/6000A-TF-4,FS3000A/6000A 4-PH 36-INCH THIN FLEXI SET
FS17X5-TF	4-Phase Flex Current Clamp Set (1735 & 1745)	TL	4174	FS17X5-TF	FS17X5-TF,3000A 4-PH FLUKE 1735 & 1745 THIN FLEXI SET
FS17XX IP65-TF	4-Phase Flex Current Clamp Set (1735/1743)	TL	4652	FS17XX IP65-TF	FS17XX IP65-TF,3000A IP65 4-PH FLUKE 1743/4 THIN FLEXI SET
FS17XX-1PH-TF	1-phase Flex Current Clamp (1735, 1743, 1744, 1745)	TL	1034	FS17XX-1PH-TF	FS17XX-1PH-TF,3000A 1PH FLUKE 1735 & 174X THIN FLEXI
3210-PR-TF	Flexible Current Transformer 20A-1000A (Fluke 1750)	TL	1962	3210-PR-TF	3210-PR-TF,1000A FLUKE 1750 THIN FLEXI 61CM (24IN)
3310-PR-TF	Flexible Current Transformer 100A-5000A (Fluke 1750)	TL	2683	3310-PR-TF	3310-PR-TF,5000A FLUKE 1750 THIN FLEXI 61CM (24IN)
3312-PR-TF	Flexible Current Transformer 100A-5000A (Fluke 1750)	TL	3289	3312-PR-TF	3312-PR-TF,5000A FLUKE 1750 THIN FLEXI 122CM (48IN)
TPS FLEX 18-TF	Flexible Current Probe 500A (Fluke 1760)	TL	1546	TPS FLEX 18-TF	TPS FLEX 18-TF,100/500A FLUKE 1760 THIN FLEXI 45CM (18IN)
TPS FLEX 24-TF	Flexible Current Probe 1000A (Fluke 1760)	TL	1546	TPS FLEX 24-TF	TPS FLEX 24-TF,200/1000A FLUKE 1760 THIN FLEXI 61CM (24IN)
TPS Flex 36-TF	Flexible Current Probe 6000A	TL	3060	TPS FLEX 36-TF	TPS FLEX 36-TF,3000/6000A FLUKE 1760 THIN FLEXI 91CM (36IN)
MBX USB-RS232	EP0328Z, USB to Serial RS232 Adapter	TL	140	MBX USB-RS232	MBX USB-RS232,EP0328Z, USB TO SERIAL RS232 ADAPTER
TPS CF-CARD	EP2523A, Compact Flash Card, 2GB	TL	3209	TPS CF-CARD	TPS CF-CARD,EP2523A, COMPACT FLASH CARD, 2GB
TPS Nullmodem Cable	A550500510, RS232 Cross Link Cable, 3M	TL	114	TPS NULLMODEM CABLE	TPS NULLMODEM CABL,A550500510, RS232 CROSS LINK CABLE, 3M
TPS Shunt 1A	A680501054, Shunt 1 A AC/DC	TL	1004	TPS SHUNT 1A	TPS SHUNT 1A,A680501054, SHUNT 1 A AC/DC
TPS/MBX DOLPH RED	EP0326Z, Dolphin Clip, Red	TL	85	TPS/MBX DOLPH RED	TPS/MBX DOLPH RED,EP0326Z, DOLPHIN CLIP, RED
VL1735/45	Banana 4-Phase Voltage Lead set for Fluke-1735/45	TL	698	VL1735/45	VL1735/45,BANANA 4-PHASE VOLTAGE LEAD SET FOR FLUKE-1735/45
I5A/50A CLAMP PQ1	1-Phase 5A/50A Mini Current Clamp set for PQ	TL	1114	I5A/50A CLAMP PQ1	I5A/50A CLAMP PQ1,1-PHASE 5A/50A MINI CURRENT CLAMP SET FOR PQ

Model	Açıklama	Para Birimi	Tavsiye edilen		Parça numarı	Ürün Tanımı
			Son Kullanıcı	Liste fiyatı		
I5S-PR	1750, 5A Current Clamp	TL	1034		I5S-PR	I5S-PR,1750, 5A CURRENT CLAMP
I430-FLEXI-TF	AC Flexible Current Clamp 3000A (430 Series)	TL	1082		I430-FLEXI-TF	I430-FLEXI-TF,6000A FLUKE 430 THIN FLEXI 61CM (24IN)
I430-FLEXI-TF-4PK	AC Flex Current Clamp 3000A, 4-pack (430 Series)	TL	3243		I430-FLEXI-TF-4PK	I430-FLEXI-TF-4PK,6000A FLUKE 430 THIN FLEXI 61CM (24IN) 4 PACK
i430-flex-4pk	AC Flex Current Clamp 3000A, 4-pack (430 Series)	TL	3598		I430-FLEX-4PK	I430-FLEX-4PK, AC FLEX CURRENT PROBE 3000A 4 PACK

Güç Analizörleri

Norma 4000

Fluke N4K 1PP42	1 PH N4k power analyzer w/42	TL	20492		FLUKE-N4K 1PP42	FLUKE-N4K 1PP42,1 PH N4K POWER ANALYZER W/42
Fluke-N4K 2PP42I	2 PH N4K Power Analyzer w/42/IFC2	TL	31321		FLUKE-N4K 2PP42I	FLUKE-N4K 2PP42I,2 PH N4K POWER ANALYZER W/42/IFC2
Fluke N4K 3PP42	3 PH N4k power analyzer w/42	TL	31499		FLUKE-N4K 3PP42	FLUKE-N4K 3PP42,3 PH N4K POWER ANALYZER W/42
Fluke N4K 3PP42I	3 PH N4k power analyzer w/42/IFC2	TL	44911		FLUKE-N4K 3PP42I	FLUKE-N4K 3PP42I,3 PH N4K POWER ANALYZER W/42/IFC2
Fluke N4K 3PP42IP	3 PH N4k power analyzer w/42/IFC2 & PI1	TL	51328		FLUKE-N4K 3PP42IP	FLUKE-N4K 3PP42IP,3 PH N4K POWER ANALYZER W/42/IFC2S & PI1
Fluke N4K 3PP50	3 PH N4k power analyzer w/50	TL	34656		FLUKE-N4K 3PP50	FLUKE-N4K 3PP50,3 PH N4K POWER ANALYZER W/50
Fluke N4K 3PP50I	3 PH N4k power analyzer w/50/IFC2	TL	48119		FLUKE-N4K 3PP50I	FLUKE-N4K 3PP50I,3 PH N4K POWER ANALYZER W/50/IFC2
Fluke N4K 3PP50IP	3 PH N4k power analyzer w/50/IFC2 & PI1	TL	54534		FLUKE-N4K 3PP50IP	FLUKE-N4K 3PP50IP,3 PH N4K POWER ANALYZER W/50/IFC2 & PI1
Fluke N4K 3PP54I	3 PH N4k power analyzer w/54/IFC2	TL	45732		FLUKE-N4K 3PP54I	FLUKE-N4K 3PP54I,3 PH N4K POWER ANALYZER W/54/IFC2
Fluke N4K 3PP54IP	3 PH N4k power analyzer w/54/IFC2 & PI1	TL	52151		FLUKE-N4K 3PP54IP	FLUKE-N4K 3PP54IP,3 PH N4K POWER ANALYZER W/54/IFC2 & PI1
Fluke N4K 3PP42B	3 PH N4k power analyzer w/42BP	TL	33093		FLUKE-N4K 3PP42B	FLUKE-N4K 3PP42B,3 PH N4K POWER ANALYZER W/42BP
Fluke N4K 3PP42IB	3 PH N4k power analyzer w/42BP/IFC2	TL	46532		FLUKE-N4K 3PP42IB	FLUKE-N4K 3PP42IB,3 PH N4K POWER ANALYZER W/42BP/IFC2
Fluke N4K 3PP42IPB	3 PH N4k power analyzer w/42BP/IFC2 & PI1	TL	52952		FLUKE-N4K 3PP42IPB	FLUKE-N4K 3PP42IPB,3 PH N4K POWER ANALYZER W/42BP/IFC2 & PI1
Fluke N4K 3PP521B	3 PH N4k power analyzer w/52BP/IFC2	TL	44282		FLUKE-N4K 3PP521B	FLUKE-N4K 3PP521B,3 PH N4K POWER ANALYZER W/52BP/IFC2

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Norma 5000					
Fluke N5K 3PP50	3 PH N5k power analyzer w/50	TL	40492	FLUKE-N5K 3PP50	FLUKE-N5K 3PP50,3 PH N5K POWER ANALYZER W/50
Fluke N5K 3PP50I	3 PH N5k power analyzer w/50/IFC2	TL	47657	FLUKE-N5K 3PP50I	FLUKE-N5K 3PP50I,3 PH N5K POWER ANALYZER W/50/IFC2
Fluke N5K 3PP50IP	3 PH N5k power analyzer w/50/IFC2 & PI1	TL	54072	FLUKE-N5K 3PP50IP	FLUKE-N5K 3PP50IP,3 PH N5K POWER ANALYZER W/50/IFC2 & PI1
Fluke-N5K 3PP50IR	3PH N5K PowerAnalyzer w/50/IFC2/PRNTR	TL	50864	FLUKE-N5K 3PP50IR	FLUKE-N5K 3PP50IR,3 PH N5K POWER ANALYZER W/50/IFC2/PRNTR
Fluke N5K 3PP54	3 PH N5k power analyzer w/54	TL	44901	FLUKE-N5K 3PP54	FLUKE-N5K 3PP54,3 PH N5K POWER ANALYZER W/54
Fluke N5K 3PP54I	3 PH N5k power analyzer w/54/IFC2	TL	52151	FLUKE-N5K 3PP54I	FLUKE-N5K 3PP54I,3 PH N5K POWER ANALYZER W/54/IFC2
Fluke N5K 3PP54IP	3 PH N5k power analyzer w/54/IFC2 & PI1	TL	58569	FLUKE-N5K 3PP54IP	FLUKE-N5K 3PP54IP,3 PH N5K POWER ANALYZER W/54/IFC2 & PI1
Fluke N5K 3PP64	3 PH N5k power analyzer w/64	TL	53665	FLUKE-N5K 3PP64	FLUKE-N5K 3PP64,3 PH N5K POWER ANALYZER W/64
Fluke N5K 3PP64I	3 PH N5k power analyzer w/64/IFC2	TL	65334	FLUKE-N5K 3PP64I	FLUKE-N5K 3PP64I,3 PH N5K POWER ANALYZER W/64/IFC2
Fluke N5K 3PP64IP	3 PH N5k power analyzer w/64/IFC2 & PI1	TL	71868	FLUKE-N5K 3PP64IP	FLUKE-N5K 3PP64IP,3 PH N5K POWER ANALYZER W/64/IFC2 & PI1
Fluke N5K 3PP54R	3 PH N5K power analyzer w/54/printer	TL	41427	FLUKE-N5K 3PP54R	FLUKE-N5K 3PP54R,3 PH N5K POWER ANALYZER W/54/PRNTR
Fluke N5K 3PP54IR	3 PH N5K power analyzer w/54/IFC2/printer	TL	54708	FLUKE-N5K 3PP54IR	FLUKE-N5K 3PP54IR,3 PH N5K POWER ANALYZER W/54/IFC2/PRNTR
Fluke N5K 3PP64R	3 PH N5K power analyzer w/64/printer	TL	57329	FLUKE-N5K 3PP64R	FLUKE-N5K 3PP64R,3 PH N5K POWER ANALYZER W/64/PRNTR
Fluke N5K 3PP64IR	3 PH N5K power analyzer w/64/IFC2/printer	TL	68415	FLUKE-N5K 3PP64IR	FLUKE-N5K 3PP64IR,3 PH N5K POWER ANALYZER W/64/IFC2/PRNTR
Fluke N5K 3PP64IPR	3 PH N5K power analyzer w/64/IFC2 & PI1/printer	TL	75077	FLUKE-N5K 3PP64IPR	FLUKE-N5K 3PP64IPR,3 PH N5K POWER ANALYZER W/64/IFC2 & PI1/PRNTR
Fluke N5K 4PP54	4 PH N5k power analyzer w/54	TL	48055	FLUKE-N5K 4PP54	FLUKE-N5K 4PP54,4 PH N5K POWER ANALYZER W/54
Fluke N5K 4PP54IP	4 PH N5k power analyzer w/54/IFC2 & PI1	TL	64030	FLUKE-N5K 4PP54IP	FLUKE-N5K 4PP54IP,4 PH N5K POWER ANALYZER W/54/IFC2 & PI1
Fluke N5K 6PP54I	FLUKE-N5K 6PP54I,6 PH N5K POWER ANALYZER W/54/IFC2	TL	73647	FLUKE-N5K 6PP54I	FLUKE-N5K 6PP54I,6 PH N5K POWER ANALYZER W/54/IFC2
Fluke N5K 6PP54IP	FLUKE-N5K 6PP54IP,6 PH N5K POWER ANALYZER W/54/IFC2 & PI1	TL	80067	FLUKE-N5K 6PP54IP	FLUKE-N5K 6PP54IP,6 PH N5K POWER ANALYZER W/54/IFC2 & PI1

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke N5K 6PP64I	6 PH N5k power analyzer w/64/IFC2	TL	91324	FLUKE-N5K 6PP64I	FLUKE-N5K 6PP64I,6 PH N5K POWER ANALYZER W/64/IFC2
Fluke N5K 6PP64IP	6 PH N5k power analyzer w/64/IFC2 & PII	TL	97860	FLUKE-N5K 6PP64IP	FLUKE-N5K 6PP64IP,6 PH N5K POWER ANALYZER W/64/IFC2 & PII
Fluke N5K 6PP50I	6 PH N5k power analyzer w/50/IFC2	TL	64618	FLUKE-N5K 6PP50I	FLUKE-N5K 6PP50I,6 PH N5K POWER ANALYZER W/50/IFC2
Fluke N5K 6PP50IP	6 PH N5K power analyzer w/50/IFC2 & PII	TL	71326	FLUKE-N5K 6PP50IP	FLUKE-N5K 6PP50IP,6 PH N5K POWER ANALYZER W/50/IFC2 & PII
Fluke N5K 6PP42IB	6 PH N5K power analyzer w/42BP/IFC2	TL	61252	FLUKE-N5K 6PP42IB	FLUKE-N5K 6PP42IB,6 PH N5K POWER ANALYZER W/42BP/IFC2
Fluke N5K 6PP54IR	6 PH N5K power analyzer w/54/IFC2/printer	TL	69263	FLUKE-N5K 6PP54IR	FLUKE-N5K 6PP54IR,6 PH N5K POWER ANALYZER W/54/IFC2/PRNTR
Fluke N5K 6PP54IPR	6 PH N5K power analyzer w/54/IFC2 & PII/printer	TL	75916	FLUKE-N5K 6PP54IPR	FLUKE-N5K 6PP54IPR,6 PH N5K POWER ANALYZER W/54/IFC2 & PII/PRNTR
Fluke N5K 6PP50IR	6 PH N5K power analyzers w/50/IFC2/printer	TL	74002	FLUKE-N5K 6PP50IR	FLUKE-N5K 6PP50IR,6 PH N5K POWER ANALYZER W/50/IFC2/PRNTR
Fluke N5K 6PP50IPR	6 PH N5K power analyzers W/50/IFC2 & PII/printer	TL	80662	FLUKE-N5K 6PP50IPR	FLUKE-N5K 6PP50IPR,6 PH N5K POWER ANALYZER W/50/IFC2 & PII/PRNTR
Fluke N5K 6PP64IR	6 PH N5K power analyzer w/64/IFC2/printer	TL	96701	FLUKE-N5K 6PP64IR	FLUKE-N5K 6PP64IR,6 PH N5K POWER ANALYZER W/64/IFC2/PRNTR
Fluke N5K 6PP64IPR	6 PH N5K power analyzer w/64/IFC2 & PII/Printer	TL	103518	FLUKE-N5K 6PP64IPR	FLUKE-N5K 6PP64IPR,6 PH N5K POWER ANALYZER W/64/IFC2 & PII/PRNTR
Fluke N5K 6PP42IBR	6 PH N5K power analyzer W/42BP/IFC2/printer	TL	70583	FLUKE-N5K 6PP42IBR	FLUKE-N5K 6PP42IBR,6 PH N5K POWER ANALYZER W/42BP/IFC2/PRNTR

Norma 4000/5000 Aksesuarları

Norma 10A shunt	Traxial Shunt	TL	3451	NORMA 10A SHUNT	NORMA 10A SHUNT,TRIAxIAL EXTERNAL SHUNT
Norma 30A shunt	Traxial Shunt	TL	3806	NORMA 30A SHUNT	NORMA 30A SHUNT,TRIAxIAL EXTERNAL SHUNT
Norma 32A shunt	32A planar shunt	TL	2369	NORMA 32A SHUNT	NORMA 32A SHUNT,32A PLANAR SHUNT
Norma 32A cables	Cables for 32A planar shunt	TL	455	NORMA 32A CABLES	NORMA 32A CABLES,CABLES FOR 32A PLANAR SHUNT
Norma 100A shunt	100 A Shunt with Cables (0.001 Ohm, 0 to 0.5 MHz)	TL	5791	NORMA 100A SHUNT	NORMA 100A SHUNT,EXTERNAL SHUNT WITH CABLES
Norma 150A shunt	150 A Shunt with Cables (0.5 mOhm, 0 to 0.5 MHz)	TL	11959	NORMA 150A SHUNT	NORMA 150A SHUNT,EXTERNAL SHUNT WITH CABLES

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Norma 300A shunt	300 A Shunt with Cables (0.1 mOhm, 0 to 1 MHz)	TL	10514	NORMA 300A SHUNT	NORMA 300A SHUNT,EXTERNAL SHUNT WITH CABLES
Norma 500A shunt	500 A Shunt with Cables (0.1 mOhm, 0 to 0.2 MHz)	TL	11838	NORMA 500A SHUNT	NORMA 500A SHUNT,EXTERNAL SHUNT WITH CABLES
Norma Lg shunt/cbl	LG Shunt Cables for High Current Shunts	TL	720	NORMA LG SHUNT/CBL	NORMA LG SHUNT/CBL,CABLES FOR HIGH CURRENT SHUNTS
Norma wye adapter	External accessory box	TL	2250	NORMA STAR POINT	NORMA STAR POINT,EXTERNAL STAR POINT ADAPTER
Fluke N4K RACK KIT	N4K 19 inch rack mount kit with handles	TL	620	FLUKE-N4K RACK KIT	FLUKE-N4K RACK KIT,N4K 19 INCH RACK MOUNT KIT W/HANDLES
Fluke N5K RACK KIT	N5K 19 inch rack mount kit with handles	TL	652	FLUKE-N5K RACK KIT	FLUKE-N5K RACK KIT,N5K 19 INCH RACK MOUNT KIT W/HANDLES

Titresim Test Cihazları

Fluke 805	Vibration Meter	TL	4796	FLUKE-805	FLUKE-805,VIBRATION METER
Fluke 810	Vibration Tester	TL	22139	FLUKE-810	FLUKE-810,VIBRATION TESTER
810S	Sensor	TL	3533	810S	810S, SENSOR
810T	Tachometer	TL	300	810T	810T,TACHOMETER
810QDC	Quick Disconnect Cable	TL	345	810QDC	810QDC,QUICK DISCONNECT CABLE
810SMM	Sensor Magnet Mount	TL	480	810SMM	810SMM,SENSOR MAGNET MOUNT
810SMP	Sensor Mounting Pads (10-pack)	TL	69	810SMP	810SMP,SENSOR MOUNTING PADS
SBP-810	Smart Battery Pack	TL	597	SBP810	SBP810,SMART BATTERY PACK
Fluke-810SC-20	SENSOR CABLE, 20 FT	TL	368	810SC-20	810SC-20,SENSOR CABLE, 20 FT
Fluke-810PA	AC Power Adapter with International Plug Set	TL	190	810PA	810PA,AC POWER ADAPTER WITH INTERNATIONAL PLUG SET

Radyasyon Olcum Cihazı

Fluke 481-DESI	Radiation meter	TL	8403		
190 HPS	Radation meter carrying case	TL	1503		

Proses Kalibratörleri

700 Serisi Proses Kalibratörleri

Fluke 705	Loop Calibrator	TL	1793	FLUKE-705	FLUKE-705,LOOP CALIBRATOR
Fluke 707	Loop Calibrator	TL	1937	FLUKE-707	FLUKE-707,LOOP CALIBRATOR
Fluke 707Ex	Intrinsically Safe Loop Calibrator	TL	2813	FLUKE- 707EX	FLUKE-707EX,MA CALIBRATOR
Fluke 709	Precision Loop Calibrator	TL	2077	Fluke 709	
Fluke 709H	Precision HART Loop Calibrator	TL	3383	Fluke 709H	

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Fluke 712	RTD Calibrator	TL	2642	FLUKE-712	FLUKE-712,RTD CALIBRATOR
Fluke 714	Thermocouple Calibrator	TL	2642	FLUKE-714	FLUKE-714,THERMOCOUPLE CALIBRATOR
Fluke 715	Volt/mA Calibrator	TL	2642	FLUKE-715	FLUKE-715,VOLT/MA CALIBRATOR
Fluke 717 1G	Pressure Calibrator (68.9 mbar)	TL	3238	FLUKE-717 1G	FLUKE-717 1G,PRESSURE CALIBRATOR 1 PSIG
Fluke 717-15G	Pressure Calibrator (1 bar)	TL	3184	FLUKE-717 15G	FLUKE-717 15G,PRESSURE CALIBRATOR 15 PSIG
Fluke 717 100G	Pressure Calibrator (7 bar)	TL	3238	FLUKE-717 100G	FLUKE-717 100G,PRESSURE CALIBRATOR, 100 PSIG
Fluke 717 30G	Pressure Calibrator (2 bar)	TL	3238	FLUKE-717 30G	FLUKE-717 30G,PRESSURE CALIBRATOR, 30 PSIG
Fluke 717 300G	Pressure Calibrator (20 bar)	TL	3238	FLUKE-717 300G	FLUKE-717 300G,PRESSURE CALIBRATOR 300 PSIG
Fluke 717 500G	Pressure Calibrator (34.7 bar)	TL	3238	FLUKE-717 500G	FLUKE-717 500G,PRESSURE CALIBRATOR 500 PSIG
Fluke 717 1000G	Pressure Calibrator (69 bar)	TL	3238	FLUKE-717 1000G	FLUKE-717 1000G,PRESSURE CALIBRATOR 1000 PSIG
Fluke 717 1500G	Pressure Calibrator (103.4 bar)	TL	3527	FLUKE-717 1500G	FLUKE-717 1500G,PRESSURE CALIBRATOR 1500 PSIG
Fluke 717 3000G	Pressure Calibrator (207 bar)	TL	3527	FLUKE-717 3000G	FLUKE-717 3000G,PRESSURE CALIBRATOR 3000 PSIG
Fluke 717 5000G	Pressure Calibrator (345 bar)	TL	3527	FLUKE-717 5000G	FLUKE-717 5000G,PRESSURE CALIBRATOR 5000 PSIG
Fluke 717-10000G	Pressure Calibrator (690 bar)	TL	3469	FLUKE-717 10000G	FLUKE-717 10000G,PRESSURE CALIBRATOR 10000 PSIG
Fluke 718 30G	Pressure Calibrator (2 bar)	TL	5855	FLUKE-718 30US	FLUKE-718 30US,PRESSURE CALIBRATOR 30 PSIG USA
Fluke 718 1G	Pressure Calibrator (68.9 mbar)	TL	5855	FLUKE-718 1G	FLUKE-718 1G,PRESSURE CALIBRATOR 1 PSIG
Fluke 718 100G	Pressure Calibrator (7 bar)	TL	5855	FLUKE-718 100US	FLUKE-718 100US,PRESSURE CALIBRATOR 100 PSIG USA
Fluke 718 300G	Pressure Calibrator (20 bar)	TL	5855	FLUKE-718 300G	FLUKE-718 300G,PRESSURE CALIBRATOR 300 PSIG
Fluke 718Ex 30G	Intrinsically Safe Pressure Calibrator (2 bar)	TL	8190	FLUKE-718EX 30	FLUKE-718EX 30,I.S. PRESSURE CALIBRATOR 30 PSIG
Fluke 718Ex 100G	Intrinsically Safe Pressure Calibrator (7 bar)	TL	8190	FLUKE-718EX 100	FLUKE-718EX 100,I.S. PRESSURE CALIBRATOR 100 PSIG
Fluke 718Ex 300G	Intrinsically Safe Pressure Calibrator (20 bar)	TL	8190	FLUKE-718EX 300	FLUKE-718EX 300,I.S. PRESSURE CALIBRATOR 300 PSIG
Fluke 719 30G	Electric Pressure Calibrator (2 bar)	TL	7696	FLUKE-719 30G	FLUKE-719 30G,ELECTRIC PRESSURE CALIBRATOR, 30 PSI, 2 BAR
Fluke 719 100G	Electric Pressure Calibrator (7 bar)	TL	7696	FLUKE-719 100G	FLUKE-719 100G, ELECTRIC PRESSURE CALIBRATOR, 100 PSI, 7 BAR
Fluke 724	Temperature Calibrator	TL	4743	FLUKE-724	FLUKE-724,TEMPERATURE CALIBRATOR
Fluke 725	Multifunction Process Calibrator	TL	6184	FLUKE-725 US	FLUKE-725 US,MULTIFUNCTION PROCESS CALIBRATOR

Model	Açıklama	Para Birimi	Tavsiye edilen		Ürün Tanımı
			Son Kullanıcı	Parça numarı	
			Liste fiyatı		
Fluke 725Ex	Intrinsically Safe Multifunction Process Calibrator	TL	8693	FLUKE-725EX	FLUKE-725EX,I.S. MULTIFUNCTION PROCESS CALIBRATOR
Fluke 726	Precision Process Calibrator	TL	8409	FLUKE-726	FLUKE-726,PRECISION MULTIFUNCTION CALIBRATOR
Fluke 753	Documenting Process Calibrator	TL	13050	FLUKE-753	FLUKE-753,DOCUMENTING PROCESS CALIBRATOR, NON BUS
Fluke 754	Documenting Process Calibrator, HART	TL	16769	FLUKE-754	FLUKE-754,DOCUMENTING PROCESS CALIBRATOR
Fluke 771	Milliamp Process Clamp Meter	TL	1443	FLUKE-771	FLUKE-771,MILLIAMP PROCESS CLAMP METER
Fluke 772	Milliamp Process Clamp Meter	TL	2022	FLUKE-772	FLUKE-772, MILLIAMP PROCESS CLAMP METER
Fluke 773	Milliamp Process Clamp Meter	TL	2886	FLUKE-773	FLUKE-773, MILLIAMP PROCESS CLAMP METER
Fluke 787/E	Process Meter	TL	2022	FLUKE-787/E	FLUKE-787/E,PROCESS METER
Fluke 789/E	Process Meter	TL	2317	FLUKE-789/E	FLUKE-789/E,PROCESS METER

Basınç Modülleri

700P00	Differential Pressure Module (2.5 mbar)	TL	4318	FLUKE-700P00	FLUKE-700P00,PRESSURE MODULE, 0-1 IN. H20 DIFF
700P01	Differential Pressure Module (25 mbar)	TL	3216	FLUKE-700P01	FLUKE-700P01,PRESSURE MODULE, 0-10 IN. H20 DIFF
700P01Ex	Differential Pressure Module (25 mbar)	TL	4695	FLUKE-700P01EX	FLUKE-700P01EX,I.S. PRESSURE MODULE, 0-10 IN. H20 DIFF
700P02	Differential Pressure Module (70 mbar)	TL	3216	FLUKE-700P02	FLUKE-700P02,PRESSURE MODULE, 0-1 PSID
700P22	Differential Pressure Module Wet (70 mbar)	TL	3216	FLUKE-700P22	FLUKE-700P22,PRESSURE MODULE, 0-1 PSID, WET
700P03	Differential Pressure Module (340 mbar)	TL	3216	FLUKE-700P03	FLUKE-700P03,PRESSURE MODULE, 0-5 PSID
700P23	Differential Pressure Module Wet (340 mbar)	TL	3216	FLUKE-700P23	FLUKE-700P23,PRESSURE MODULE, 0-5 PSID, WET
700P04	Differential Pressure Module (1000 mbar)	TL	3216	FLUKE-700P04	FLUKE-700P04,PRESSURE MODULE, 0-15 PSID
700P24	Differential Pressure Module Wet (1000 mbar)	TL	3216	FLUKE-700P24	FLUKE-700P24,PRESSURE MODULE, 0-15 PSID, WET
700P24Ex	Differential Pressure Module Wet (1001 mbar)	TL	4695	FLUKE-700P24EX	FLUKE-700P24EX,I.S. PRESSURE MODULE, 0-15 PSID, WET
700P05	Gage Pressure Module (2 bar)	TL	3216	FLUKE-700P05	FLUKE-700P05,PRESSURE MODULE, 0-30 PSIG
700P05Ex	Gage Pressure Module (2 bar)	TL	4695	FLUKE-700P05EX	FLUKE-700P05EX, I.S. PRESSURE MODULE, 0-30 PSIG
700P06	Gage Pressure Module (7 bar)	TL	3216	FLUKE-700P06	FLUKE-700P06,PRESSURE MODULE, 0-100 PSIG

Model	Açıklama	Para Birimi	Tavsiye edilen		Ürün Tanımı
			Son Kullanıcı	Parça numarı	
			Liste fiyatı		
700P06Ex	Gage Pressure Module (7 bar)	TL	4695	FLUKE-700P06EX	FLUKE-700P06EX, I.S. PRESSURE MODULE, 0-100 PSIG
700P27	Gage Pressure Module (20 bar)	TL	3216	FLUKE-700P27	FLUKE-700P27,PRESSURE MODULE, 300 PSIG
700P27Ex	Gage Pressure Module (20 bar)	TL	4695	FLUKE-700P27EX	FLUKE-700P27EX,I.S. PRESSURE MODULE, 300 PSIG
700P07	Gage Pressure Module (34 bar)	TL	3216	FLUKE-700P07	FLUKE-700P07,PRESSURE MODULE, 0-500 PSIG
700P08	Gage Pressure Module (70 bar)	TL	3216	FLUKE-700P08	FLUKE-700P08,PRESSURE MODULE, 0-1000 PSIG
700P09	Gage Pressure Module (100 bar)	TL	3216	FLUKE-700P09	FLUKE-700P09,PRESSURE MODULE 1500PSIG
700P09Ex	Gage Pressure Module (100 bar)	TL	4695	FLUKE-700P09EX	FLUKE-700P09EX, I.S. PRESSURE MODULE 1500 PSIG
700P29	Gage Pressure Module (200 bar)	TL	5244	FLUKE-700P29	FLUKE-700P29,PRESSURE MODULE,3000PSIG WET
700P29Ex	Gage Pressure Module (200 bar)	TL	8034	FLUKE-700P29EX	FLUKE-700P29EX,I.S. PRESSURE MODULE,3000PSIG WET
700P30	Gage Pressure Module (340 bar)	TL	5244	FLUKE-700P30	FLUKE-700P30,PRESSURE MODULE,5000PSIG WET
700P31	Gage Pressure Module (700 bar)	TL	5244	FLUKE-700P31	FLUKE-700P31,PRESSURE MODULE,10000PSIG WET
700PA3	Absolute Pressure Module (340 mbar)	TL	3707	FLUKE-700PA3	FLUKE-700PA3,PRESSURE MODULE 0-5PSIA
700PA4	Absolute Pressure Module (1000 mbar)	TL	3707	FLUKE-700PA4	FLUKE-700PA4,PRESSURE MODULE 0-15PSIA
700PA4Ex	Absolute Pressure Module (1000 mbar)	TL	5205	FLUKE-700PA4EX	FLUKE-700PA4EX,I.S. PRESSURE MODULE 0-15 PSIA
700PA5	Absolute Pressure Module (2 bar)	TL	3707	FLUKE-700PA5	FLUKE-700PA5,PRESSURE MODULE 0-30PSIA
700PA6	Absolute Pressure Module (7 bar)	TL	3707	FLUKE-700PA6	FLUKE-700PA6,PRESSURE MODULE 0-100PSIA
700PCK	Pressure Module Calibration Kit	TL	2594	FLUKE-700PCK	FLUKE-700PCK,PRESSURE MODULE CALIBRATION KIT
700PD2	Dual Pressure Module (± 70 mbar)	TL	3707	FLUKE-700PD2	FLUKE-700PD2,PRESSURE MODULE +/-1 PSID
700PD3	Dual Pressure Module (± 340 mbar)	TL	3707	FLUKE-700PD3	FLUKE-700PD3,PRESSURE MODULE +/-5 PSID
700PD4	Dual Pressure Module (± 1000 mbar)	TL	3707	FLUKE-700PD4	FLUKE-700PD4,PRESSURE MODULE, +/-15PSID
700PD5	Dual Pressure Module (-1000/+2000 mbar)	TL	3707	FLUKE-700PD5	FLUKE-700PD5,PRESSURE MODULE -15+30 PSIG
700PD6	Dual Pressure Module (-1000 mbar/+6.9 bar)	TL	3707	FLUKE-700PD6	FLUKE-700PD6,PRESSURE MODULE -15+100PSIG
700PD7	Dual Pressure Module (-1000 mbar/+13.8 bar)	TL	3707	FLUKE-700PD7	FLUKE-700PD7,PRESSURE MODULE -15+200PSIG
700PV3	Vacuum Pressure Module (-340 mbar)	TL	3707	FLUKE-700PV3	FLUKE-700PV3,PRESSURE MODULE -5PSID
700PV4	Vacuum Pressure Module(-1000 mbar)	TL	3707	FLUKE-700PV4	FLUKE-700PV4,PRESSURE MODULE -15PSID

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
700G04	Pressure gauge(1 bar)	TL	2337	FLUKE-700G04	FLUKE-700G04,PRESSURE GAUGE, 15 PSIG
700G05	Pressure gauge (2 bar)	TL	2337	FLUKE-700G05	FLUKE-700G05,PRESSURE GAUGE, 30 PSIG
700G06	Pressure gauge (6.9 bar)	TL	2337	FLUKE-700G06	FLUKE-700G06,PRESSURE GAUGE, 100 PSIG
700G27	Pressure gauge (20 bar)	TL	2337	FLUKE-700G27	FLUKE-700G27,PRESSURE GAUGE, 300 PSIG
700G07	Pressure gauge (34 bar)	TL	2337	FLUKE-700G07	FLUKE-700G07,PRESSURE GAUGE, 500 PSIG
700G08	Pressure gauge (69 bar)	TL	2337	FLUKE-700G08	FLUKE-700G08,PRESSURE GAUGE, 1,000 PSIG
700G29	Pressure gauge (200 bar)	TL	2417	FLUKE-700G29	FLUKE-700G29,PRESSURE GAUGE, 3,000 PSIG
700G30	Pressure gauge (340 bar)	TL	2417	FLUKE-700G30	FLUKE-700G30,PRESSURE GAUGE, 5,000 PSIG
700G31	Pressure gauge (690 bar)	TL	2417	FLUKE-700G31	FLUKE-700G31,PRESSURE GAUGE, 10,000 PSIG
700G/TRACK	Data logging cable & software	TL	1292	700G/TRACK	700G/TRACK,DATA LOGGING CABLE & SOFTWARE
700HTPK	Hydraulic test pump kit, 0 to 10.000 psi	TL	3383	FLUKE-700HTPK	FLUKE-700HTPK,HYDRAULIC TEST PUMP KIT, 0 TO 10000 PSI/700 BAR
700PTPK	Pneumatic test pump kit, 0 to 600 psi	TL	1683	FLUKE-700PTPK	FLUKE-700PTPK,PNEUMATIC TEST PUMP KIT, 0 TO 600 PSI/40 BAR

Basınç Modülleri

700BCA	Bar Code Adapter	TL	140	FLUKE-700BCA	FLUKE-700BCA,BAR CODE ADAPTER
700BCW	Bar Code Wand	TL	1395	FLUKE-700BCW	FLUKE-700BCW,BAR CODE WAND
700HTH-1	Hydraulic Test Hose	TL	1240	FLUKE-700HTH-1	FLUKE-700HTH-1,HYDRAULIC TEST HOSE, 10,000 PSI/690 BAR
700ILF	In-Line Filter	TL	151	FLUKE-700ILF	FLUKE-700ILF,IN-LINE FILTER,1 MICRON,100 PSI
700LTP-1	Low Pressure Test Pump	TL	1811	FLUKE-700LTP-1	FLUKE-700LTP-1,LOW-PRESSURE TEST PUMP, 100 PSI/7 BAR
700-IV	Current Shunt	TL	901	FLUKE-700-IV	FLUKE-700-IV,CURRENT SHUNT
700PMP	Pressure Pump (10 bar)	TL	1095	FLUKE-700PMP	FLUKE-700PMP,PRESSURE PUMP
700PRV-1	Pressure Relief Valve for 700HTP	TL	1670	FLUKE-700PRV-1	FLUKE-700PRV-1,PRESSURE RELIEF VALVE KIT
700PTP-1	Pneumatic Test Pump	TL	1702	FLUKE-700PTP-1	FLUKE-700PTP-1,PNEUMATIC TEST PUMP. -13 TO 600 PSI
700SC	Serial Interface Cable (Fluke 725/725Ex/726)	TL	336	FLUKE-700SC	FLUKE-700SC,CABLE ASSEMBLY, SERIAL INTERFACE
700SW	DPC/Track Software	TL	6443	FLUKE-700SW	FLUKE-700SW,DPC/TRACK
700TC1	Thermocouple Plug Kits (10 types)	TL	236	FLUKE-700TC1	FLUKE-700TC1,TC MINI-PLUG KIT (TEN TYPES)
700TC2	Thermocouple Plug Kits (5 types)	TL	215	FLUKE-700TC2	FLUKE-700TC2,T/C MINI-PLUG KIT TYPE J,K,T,E,R,S
744V20	HART Upgrade	TL	1105	FLUKE-744V20	FLUKE-744V20,HART UPGRADE

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
787CAL 230	Calibration Module (Fluke 787)	TL	1866	FLUKE-787CAL230	FLUKE-787CAL230,CALIBRATION MODULE, EUROPE
BC7217	Battery Charger	TL	485	BC7217 INTL	BC7217 INTL,BATTERY CHARGER, NIMH
BE9005 220	Battery Eliminator	TL	595	BE9005 220	BE9005 220,BATTERY ELIMINATOR
BE9005 240	Battery Eliminator	TL	595	BE9005 240	BE9005 240,BATTERY ELIMINATOR
BP7235	NiMH Battery Pack	TL	595	BP7235	BP7235,NIMH BATTERY PACK
C700	Hard Case (700 Series)	TL	572	C700	C700,HARD CARRYING CASE (700 SERIES)
C789	Soft Meter Case	TL	295	C789	C789,SOFT CARRYING CASE
FVF-SC2	FlukeView Forms Software + IR USB-Cable (180 Series, 1653, 789, 1550B)	TL	560	FVF-SC2	FVF-SC2,FLUKEVIEW FORMS WITH CABLE FOR USE WITH 18X, 28X DMMS
FVF-Basic	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	TL	359	FVF-BASIC	FVF-BASIC,FLUKEVIEW FORMS W/CABLE FOR 180 SERIES AND 789
Fluke 700HTP-2	Hydraulic Test Pump, 690 bar	TL	2509	FLUKE-700HTP-2	FLUKE-700HTP-2,HYDRAULIC TEST PUMP, 10,000 PSI/690 BAR
IR189USB	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	TL	133	IR189USB	IR189USB, USB CABLE FOR FLUKE-18X, 28X DMMS
BP7240	753/754 Spare Battery	TL	391	BP7240	BP7240,BATTERY PACK, FLUKE 75X
Fluke 750SW	DPC/TRACK2-software	TL	7979	FLUKE-750SW	FLUKE-750SW,DPC/TRACK2
BC7240	Battery Charger (753/754)	TL	105	BC-7240	BC-7240,BATTERY CHARGER, FLUKE 75X
HART DRYWELL CABLE	CABLE KIT, HART DRYWELLCONTR OL	TL	446	HART DRYWELL CABLE	HART DRYWELL CABLE,CABLE KIT, HART DRYWELL CONTROL
Fluke-71x	Fluke - 71X Hose Kit Accessory	TL	288	FLUKE-71X	FLUKE-71X,HOSE KIT ACCESSORY
Fluke 700TLK	Process Test Lead Kit	TL	313	FLUKE-700TLK	FLUKE-700TLK,PROCESS CALIBRATION DELUXE TEST LEAD KIT
Fluke 709H/TRACK	Logging software with cable	TL	1031	Fluke 709H/TRACK K	

Genel Aksesuarlar

Test Uçları, Problar ve Klipsler

80K-15	PROBE, ELECTRONIC AIR CLEANER	TL	560	80K-15	80K-15,PROBE, ELECTRONIC AIR CLEANER
AC175	Threaded Alligator Clip Set	TL	64	AC175	
AC220	SureGrip Alligator Clip Set	TL	91	AC220	AC220,SUREGRIP ALLIGATOR CLIP
AC280	SureGrip Hook Clip Set	TL	82	AC280	AC280,SUREGRIP HOOK CLIPS
AC283	SureGrip Pincer Clip Set	TL	91	AC283	AC283,SUREGRIP PINCER CLIPS

Model	Açıklama	Para Birimi	Tavsiye edilen		Ürün Tanımı
			Son Kullanıcı	Liste fiyatı	
AC285	SureGrip Alligator Clip Set	TL	50	AC285	AC285,SUREGRIP LARGE ALLIGATOR CLIP
AC285-FTP	Alligator Clips and adaptors (FTP-1, FTPL-1)	TL	75	AC285-FTP	AC285-FTP,ALLIGATOR CLIPS, FTP, FTPL, FTP-1, FTPL-1
AC87	Heavy Duty Bus Bar Clip Set	TL	96	AC87	AC87,TEST LEAD ACCESSORY BUS BAR CLIP
AC89	Heavy Duty Insulation Piercing Test Clip	TL	96	AC89	AC89,INSULATION PIERCING CLIP
BP980	Dual Banana Plug Kit	TL	91	BP980	BP980,DUAL BANANA PLUG KIT
FTP-1	Fuse test probe set	TL	208	FTP-1	FTP-1,FUSE TEST PROBE SET
FTPL-1	Fuse test probe set with test leads	TL	236	FTPL-1	FTPL-1,FUSE TEST PROBE SET WITH TEST LEADS
H900	Test Lead Holder	TL	53	H900	H900,TEST LEAD HOLDER
LEADWRAP	Durable Nylon Hook and Loop Fastener, 3 pack	TL	16	LEADWRAP	LEADWRAP,DURABLE FLUKE NYLON HOOK AND LOOP FASTENER, 3 PK
T5-Kit	T5 Tester Accessory Starter Kit	TL	133	T5-KIT-1	T5-KIT-1,T5 TESTER ACCESSORY STARTER KIT,031
T5-RLS	Replacement Test Lead Set (T5)	TL	62	T5-RLS	T5-RLS,REPLACEMENT TEST LEAD SET FOR T5
TL175	Twist Guard Test Leads	TL	64	TL175	TL175,TWISTGUARDTM TEST LEADS, 2MM DIA PROBE TIPS
TL175E	Twist Guard Test Leads, 4mm	TL	71	TL175E	TL175E, TWISTGUARDTM TEST LEADS, 2MM DIA PROBE TIPS WITH 4MM ADAPTERS
TL220-1	SureGrip Industrial Test Lead Set	TL	176	TL220-1	TL220-1,SUREGRIP INDUSTRIAL TEST LEAD SET,031
TL221	SureGrip Extension Lead Set	TL	66	TL221	TL221,SUREGRIP SILICONE TEST LEAD EXTENSION KIT
TL222	SureGrip Silicone Test Lead Set	TL	66	TL222	TL222,SUREGRIP SILICONE RIGHT ANGLE TEST LEAD SET
TL223-1	SureGrip Electrical Test Lead Set	TL	162	TL223-1	TL223-1,SUREGRIP ELECTRICAL TEST LEAD SET,031
TL224	SureGrip Silicone Test Lead Set	TL	66	TL224	TL224,SUREGRIP SILICONE TEST LEADS
TL225-1	Stray Voltage Eliminator test Lead Set	TL	254	TL225-1	TL225-1,STRAY VOLTAGE ELIMINATOR TEST LEAD SET,031
TL238	SureGrip High Energy Test Lead Kit	TL	169	TL238	TL238,TEST LEAD SET FOR HIGH ENERGY ENVIRONMENT
TL27	Heavy Duty Test Lead Set	TL	82	TL27	TL27,HEAVY DUTY TEST LEAD SET
TL40	Retractable Tip Test Lead Set	TL	103	TL40	TL40,RETRACTABLE TIP TEST LEAD SET
TL71-1	TL71, Test Lead Set	TL	64	TL71-1	TL71-1, TEST LEAD SET,PREMIUM DMM,031
TL75-1	TL75, Test Lead Set	TL	50	TL75-1	TL75-1,TEST LEAD SET,031
TL76	All-in-one Test Lead Set	TL	75	TL76	TL76,2/4 MM PROBE AND SILICONE TEST LEAD SET
TL80A-1	TL80A, Test Lead Set	TL	158	TL80A-1	TL80A-1,TEST LEAD SET,BASIC ELECTRONIC,031
TL81A	Deluxe Electronic Test Lead Kit	TL	343	TL81A	TL81A,TEST LEAD SET,DELUXE ELECTRONIC

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numar:	Ürün Tanımı
TL910	Electronic Test Lead Set (with replacement tips)	TL	142	TL910	TL910,ELECTRONIC TEST PROBES WITH REPLACEMENT TIPS
TL930	Patch Cords (60 cm)	TL	39	TL930	TL930,24 INCH PATCH CORDS
TL932	Patch Cords (90 cm)	TL	41	TL932	TL932,36 INCH PATCH CORDS
TL935	Patch Cord Kit (60, 90, 120 cm)	TL	107	TL935	TL935,PATCH CORD KIT
TL940	Mini-Hook Test Lead Set	TL	53	TL940	TL940,MINI-HOOK TEST LEADS
TL950	Mini-Pincer Test Lead Set	TL	96	TL950	TL950,MINI-PINCER TEST LEADS
TL960	Micro-Hook Test Lead Set	TL	71	TL960	TL960,MICRO-HOOK TEST LEADS
TL970	Hook and Pincer Test Lead Kit	TL	204	TL970	TL970,HOOK AND PINCER TEST LEAD KIT
TLK220	SureGrip Accessory Kit	TL	320	TLK-220 EUR	TLK-220 EUR,SUREGRIP ACCESSORY SET WITH METER CARRY CASE
TLK-225	TLK225, SureGrip Master Set	TL	343	TLK-225-1	TLK-225-1,SUREGRIP MASTER ACCESSORY SET,031
TLK281-1	TLK281, Automotive Test Lead Kit	TL	320	TLK281-1	TLK281-1,AUTOMOTIVE TEST LEAD KIT,031
TLK-282-1	TLK282, DeLuxe Automotive Test Lead Kit	TL	405	TLK282-1	TLK282-1,DELUXE AUTOMOTIVE TEST LEAD KIT,031
TLK287	Electronic Master Test Lead Kit	TL	352	TLK287	TLK287,ELECTRONICS MASTER TEST LEAD SET
TLK289	Industrial Master Test Lead Kit	TL	352	TLK289 EUR	TLK289 EUR,INDUSTRIAL MASTER TEST LEAD SET, EUROPE ONLY
TLK290	Test Probe Kit	TL	176	TLK290	TLK290,PHASE ROTATION TEST LEAD KIT
TLK291	Fused Test Probe Set	TL	176	TLK291	TLK291,FUSED TEST PROBE SET
TP1-1	TP1, Test Probes	TL	41	TP1-1	TP1-1,TEST PROBES, SLIM-REACH, FLAT BLADE,031
TP175	TwistGuard test Probes, 2MM dia probe tips	TL	41	TP175	TP175,TWISTGUARDTM TEST PROBES, 2MM DIA PROBE TIPS
TP175E	TwistGuard Test Probes, 2mm dia probe tips with 4mm adapters	TL	46	TP175E	TP175E,TWISTGUARDTM TEST PROBES, 2MM DIA PROBE TIPS WITH 4MM ADAPTERS
TP2-1	TP2, Test Probes	TL	41	TP2-1	TP2-1,TEST PROBES, SLIM-REACH, 2MM DIAMETER,031
TP220-1	TP220, SureGrip Test Probes	TL	41	TP220-1	TP220-1,SUREGRIP TEST PROBES,031
TP38	Slim Reach Test Probe Set (insulated)	TL	41	TP38	TP38,INSULATED TEST PROBE
TP74	Lantern Tip Test Probe Set	TL	41	TP74	TP74, TEST LEAD ACCESSORY SET,LANTERN TIP TEST PROBE,RED/BLACK
TP80	Electronic Test Probe Set	TL	82	TP80	TP80,ELECTRONIC TEST PROBES
TP912	Replacement tips for TL910	TL	71	TP912	TP912,REPLACEMENT TIPS FOR ELECTRONIC TEST PROBE(TL910)
TP920	Test Probe Adapter Kit	TL	91	TP920	TP920,TEST PROBE ADAPTER KIT

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Akim Pensleri					
80i-110s	AC/DC Current Clamp (100 A)	TL	1736	80I-110S	80I-110S,AC/DC CURRENT PROBE, SCOPEMETER(R)
90i-610s	AC/DC Current Clamp (600 A)	TL	1004	90I-610S	90I-610S,AC/DC CURRENT PROBE
i1000s	AC Current Clamp (1000 A)	TL	1333	I1000S	I1000S,AC CURRENT CLAMP
i1010	AC/DC Current Clamp (1000 A)	TL	935	I1010	I1010,AC/DC CURRENT CLAMP,1000A DC,600A AC
i1010 Kit	AC/DC Current Clamp (1000 A) with Soft Case	TL	1006	I1010-KIT	I1010-KIT,AC/DC CURRENT CLAMP WITH METER CARRY CASE
i200	AC Current Clamp (200 A)	TL	368	I200	I200,200 AMP CLAMP, CURRENT OUTPUT, BANANA
i2000 flex	AC Flexible Current Clamp (2000 A)	TL	881	I2000 FLEX	I2000 FLEX,AC CURRENT PROBE
i200s	AC Current Clamp (200 A)	TL	569	I200S	I200S,200 AMP CLAMP, VOLTAGE OUTPUT, BNC
i30	AC/DC Current Clamp (30A)	TL	1118	I30	I30,AC/DC CURRENT CLAMP
i3000 flex-4PK	AC Flexible Current Clamp (3000 A), 4-pack	TL	2998	I3000 FLEX-4PK	I3000 FLEX-4PK,AC CURRENT PROBE,4 PACK
i3000s	AC Current Clamp (3000 A)	TL	1480	I3000S	I3000S,AC CURRENT CLAMP
i3000s flex-24	AC Flexible Current Clamp (3000 A), 610 mm	TL	1230	I3000S FLEX-24	I3000S FLEX-24,AC CURRENT PROBE
i3000s flex-36	AC Flexible Current Clamp (3000 A), 915 mm	TL	1489	I3000S FLEX-36	I3000S FLEX-36,AC CURRENT PROBE
i30s	AC/DC Current Clamp (30A)	TL	1489	I30S	I30S,AC/DC CURRENT CLAMP
i310s	AC/DC Current Clamp (300A)	TL	993	I310S	I310S,AC/DC CURRENT CLAMP
i400	AC Current Clamp (400 A)	TL	368	I400	I400,AC CURRENT CLAMP-ON PROBE
i400s	AC Current Clamp (400A)	TL	656	I400S	I400S,AC CURRENT CLAMP-ON PROBE
I40S-PR (1750)	40A Current Clamp (1750)	TL	1034	I40S-PR	I40S-PR,1750, 40A CURRENT CLAMP
i410	AC/DC Current Clamp (400 A)	TL	576	I410	I410,400A AC/DC CURRENT CLAMP
i410 Kit	AC/DC Current Clamp (400 A) with Soft Case	TL	718	I410-KIT	I410-KIT,AC/DC CURRENT CLAMP WITH CARRY CASE
i430-flex	AC Flexible Current Clamp 3000A (430 Series)	TL	1102	I430-FLEX	I430-FLEX, AC FLEX CURRENT PROBE 3000A
i50s	AC Current Clamp (50 MHz)	TL	5651	I50S	I50S,AC/DC SCOPE CURRENT PROBE,50MHZ
i6000s flex-24	AC Current Clamp (6000 A)	TL	1557	I6000S FLEX-24	I6000S FLEX-24,AC CURRENT PROBE
i6000s flex-36	AC Current Clamp (6000 A)	TL	1798	I6000S FLEX-36	I6000S FLEX-36,AC CURRENT PROBE
i800	AC Current Clamp (800 A)	TL	727	I800	I800,AC CURRENT CLAMP
PSi50s	Bench Power Supply Module	TL	2399	PSI50S	PSI50S,BENCH POWER SUPPLY MODULE,150S

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
Sıcaklık Aksesuarları					
80AK-A	Thermocouple Adapter	TL	64	80AK-A	80AK-A,TYPE K, THERMOCOUPLE ADAPTER
80BK-A	Integrated DMM Temperature Probe (Type K)	TL	96	80BK-A	80BK-A,TYPE K, INTEGRATED DMM PROBE
80CJ-M	Male Mini Connectors (Type J)	TL	66	80CJ-M	80CJ-M,MINI THERMOCOUPLE CONNECT,TYPE J,MALE
80CK-M	Male Mini Connectors (Type K)	TL	66	80CK-M	80CK-M,MINI THERMOCOUPLE CONNECT,TYPE K,MALE
80PJ-1	Bead Probe (Type J)	TL	71	80PJ-1	80PJ-1, TYPE J BEAD PROBE,THERMOCOUPLE ASSEMBLY,TYPE J,BEADED,TYPE J,48 IN,BULK
80PJ-9	General Purpose Probe (Type J)	TL	133	80PJ-9	80PJ-9,TYPE J LANCE TIP PROBE,THERMOCOUPLE ASSEMBLY,TYPE J,LANCE TIP PROBE,MOLDED PLUG,1M,BULK
80PJ-EXT	Extension Wire Kit (Type J)	TL	128	80PJ-EXT	80PJ-EXT,TYPE J EXTENSION KIT, THERMOCOUPLE ASSEMBLY, 3 METERS
80PK-1	Bead Probe (Type K)	TL	75	80PK-1	80PK-1,PROBE, THERMOCOUPLE, BEADED K-TYPE
80PK-10	Pipe Clamp Temperature Probe (Type K)	TL	503	80PK-10	80PK-10,TYPE-K, PIPE CLAMP THERMOCOUPLE PROBE, 1.25-2.5
80PK-11	Velcro Temperature Probe	TL	96	80PK-11	80PK-11,K-TYPE VELCRO TEMPERATURE PROBE
80PK-18 Kit	Pipe Clamp Temperature Probe Kit	TL	800	80PK-18	80PK-18,TYPE K PIPE CLAMP THERMOCOUPLE PROBE KIT, 0-2.5
80PK-22	SureGrip Immersion Probe	TL	220	80PK-22	80PK-22,SUREGRIP, IMMERSION TEMPERATURE PROBE
80PK-24	SureGrip Air Probe	TL	270	80PK-24	80PK-24,SUREGRIP, AIR TEMPERATURE PROBE
80PK-25	SureGrip Piercing Probe	TL	254	80PK-25	80PK-25,SUREGRIP, PIERCING TEMPERATURE PROBE, K-TYPE
80PK-26	SureGrip General Purpose Probe	TL	270	80PK-26	80PK-26, SUREGRIP, TAPERED TEMPERATURE PROBE
80PK-27	SureGrip Industrial Surface Probe	TL	718	80PK-27	80PK-27,SUREGRIP, INDUSTRIAL SURFACE TEMPERATURE PROBE
80PK-3A	Surface Probe (Type K)	TL	359	80PK-3A	80PK-3A,PROBE,SURFACE
80PK-8	Pipe Clamp Temperature Probe (Type K)	TL	398	80PK-8	80PK-8,TYPE-K, PIPE CLAMP THERMOCOUPLE PROBE
80PK-9	General Purpose Probe (Type K)	TL	133	80PK-9	80PK-9,TYPE K LANCE TIP PROBE,THERMOCOUPLE ASSEMBLY,TYPE K,LANCE TIP PROBE,MOLDED PLUG,1M,BULK
80PK-EXT	Extension Wire Kit (Type K)	TL	128	80PK-EXT	80PK-EXT,TYPE K EXTENSION KIT, THERMOCOUPLE ASSEMBLY, 3 METERS
80PR-60	RTD Temperature Probe (Fluke 66/68)	TL	204	80PR-60	80PR-60, IR-PISTOL-RTD PROBE
80PT-25	SureGrip Piercing Probe	TL	254	80PT-25	80PT-25,SUREGRIP, PIERCING TEMPERATURE PROBE, T-TYPE

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
80PT-EXT	Extension Wire Kit (Type T)	TL	128	80PT-EXT	80PT-EXT,TYPE T EXTENSION KIT, THERMOCOUPLE ASSEMBLY, 3 METERS
80T-150UA	Universal Temperature Probe (for DMMs)	TL	569	80T-150UA	80T-150UA,PROBE,TEMPERATURE
80TK	Thermocouple Module (Type K)	TL	320	80TK	80TK,THERMOCOUPLE MODULE
Çantalar ve Kiliflar					
C10	Meter Holster	TL	75	C10	C10,HOLSTER
C100	Hard Meter and Accessory Case	TL	128	C100	C100,UNIVERSAL CARRYING CASE
C101	Hard Case	TL	142	C101	C101,HARD CASE
C115	Soft Meter Case	TL	75	C115	C115,CARRYING CASE, POLYESTER, BLK/YEL
C116	Soft Meter Case	TL	91	C116	C116,CARRYING CASE, POLYESTER, BLK/YEL
C120	Hard Case (43B/120 Series)	TL	274	C120	C120,HARD CARRYING CASE FOR 120 SERIES
C125	Soft Meter Case	TL	101	C125	C125,COMPACT SOFT CASE 120 SERIES
C12A	Soft Meter Case	TL	75	C12A	C12A,SOFT CARRYING CASE
C1600	Meter and Accessory Case	TL	137	C1600	C1600,METER GEAR BOX
C190	Hard Case (190 Series)	TL	446	C190	C190,HARDCASE SM 190 SERIES
C195	Soft Case	TL	423	C195	C195,SOFTCASE
C20	Hard Meter Case	TL	142	C20	C20,HARD CARRYING CASE FOR FLUKE-25/27
C23	Soft Meter Case	TL	75	C23	C23,SOFT CASE, VINYL,BLACK
C25	Soft Meter Case	TL	91	C25	C25,SOFT CASE FOR FLUKE-25/27/8025A
C280	Soft Meter Case	TL	87	C280	C280,CARRYING CASE, POLYESTER, BLK/YEL
C33	Soft Meter Case	TL	75	C33	C33,SOFT CASE, VINYL,BLACK/YELLOW
C345	Soft Case	TL	199	C345	C345,SOFT CARRYING CASE, POLYESTER, BLK/YEL
C35	Soft Meter Case	TL	53	C35	C35,CARRYING CASE, POLYESTER, BLK/YEL
C43	Soft Meter Case	TL	176	C43	C43,SOFT CARRYING CASE
C50	Soft Meter Case	TL	91	C50	C50,CARRYING CASE
C510	Leather Meter Case	TL	158	C510	C510,METER CASE,LEATHER,LARGE
C520A	Leather Tester Case	TL	128	C520A	C520A,TESTER CASE,LEATHER
C550	Tool Bag	TL	224	C550	C550,PREMIUM TOOL BAG
C75	Soft Accessory Case	TL	46	C75	C75,CARRYING CASE
C781	Soft Meter Case	TL	142	C781	C781,SOFT CARRYING CASE
C789	Soft Meter Case	TL	295	C789	C789,SOFT CARRYING CASE
C800	Hard Meter and Accessory Case	TL	128	C800	C800,CARRYING CASE
C90	Soft Meter Case	TL	91	C90	C90,CARRYING CASE
CXT170	Rugged Pelican Hard Case	TL	455	CXT170	CXT170,RUGGED PELICAN HARD CASE, 170 SERIES
CXT280	Rugged Pelican Hard Case	TL	455	CXT280	CXT280,RUGGED PELICAN HARD CASE, 280 SERIES

Model	Açıklama	Para Birimi	Tavsiye edilen		Ürün Tanımı
			Son Kullanıcı	Parça numar:	
			Liste fiyatı		
CXT80	Rugged Pelican Hard Case	TL	455	CXT80	CXT80,RUGGED PELICAN HARD CASE, 80/180 SERIES
H3	Holster (330 Series)	TL	82	H3	H3,HOLSTER WITH ACCESSORY POCKET,333 - 337 CLAMP METERS
H5	Electrical Tester Holster (Fluke T5)	TL	75	H5	H5,HOLSTER,BELT,ACCESSORY
H6	Infrared Thermometer Holster (Fluke 63/65/68/561)	TL	107	H6	H6, IR-PISTOL-HOLSTER
H80M	Holster + Magnetic Hanger	TL	107	H80M	H80M,PROTECTIVE HOLSTER WITH MAGNETIC HANGING STRAP

Otomotiv Grubu Aksesuarları

90i-610s	AC/DC Current Clamp (600 A)	TL	1004	90I-610S	90I-610S,AC/DC CURRENT PROBE
BP880	BNC to Female Double Stacking Banana Plug	TL	46	BP880	BP880,BNC FEMALE TO DOUBLE STACKING BANANA PLUG
BP881	BNC to Male Double Stacking Banana Plug	TL	53	BP881	BP881,BNC MALE TO DOUBLE STACKING BANANA PLUG
PV350	Pressure Vacuum Module	TL	1054	PV350	PV350,PRESSURE/VACUUM MODULE
RPM80	Inductive Pick-up Automotive	TL	194	RPM80	RPM80,INDUCTIVE PICK-UP
SCC128	Accessory Kit (120 Series)	TL	1921	SCC 128	SCC 128,AUTOMOTIVE ACC KIT 120 SERIES
SCC198	Automotive Accessory Kit (190 Series)	TL	2237	SCC 198	SCC 198,AUTOMOTIVE ACC KIT 190 SERIES
STL90	Automotive Shielded Test Lead Set (120/190 Series)	TL	533	STL90	STL90,SHIELDED TESTLEAD SET - STL90
TAS90	Automotive Accessory Set (120/190 Series)	TL	174	TAS90	TAS90,SHIELDED TEST LEAD ACC. SET
TL28A	Automotive Test Lead Set	TL	112	TL28A	TL28A,HEAVY DUTY TEST LEAD SET
TL82	Automotive Pin and Socket Adapter Set	TL	240	TL82	TL82,AUTOMOTIVE PIN AND SOCKET ADAPTER SET
TP40	Automotive Back Probe Pins (5 pcs) (4 mm)	TL	91	TP40	TP40,AUTOMOTIVE BACK PROBE PIN SET
TP81	Insulation Piercing Clip Set (4 mm)	TL	128	TP81	TP81,INSULATION PIERCING PROBES WITH BANANA JACK
TP82	Insulation Piercing Clip Set (2 mm)	TL	128	TP82	TP82,INSULATION PIERCING PROBES FOR PROBE TIPS
TP88	Rigid Back Probe Pin Set	TL	39	TP88	TP88,RIGID BACKPROBE PIN SET

Diğer Aksesuarlar

80K-40	High Voltage Probe	TL	503	80K-40	80K-40,PROBE, HIGH VOLTAGE
80K-6	High Voltage Probe	TL	286	80K-6	80K-6,PROBE, HIGH VOLTAGE
AN5	Analog Data Cable (574, 576)	TL	208	AN5	AN5,CABLE, ANALOG OUTPUT 1.5 M (5F) FOR FLUKE-57X SERIES

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
BP189	High Capacity Battery Enclosure (Fluke 189)	TL	137	BP189	BP189,HIGH CAPACITY BATTERY PACK FOR FLUKE 180 SERIES
External Battery Charger	External Battery Charger	TL	261	EBC290	EBC290,EXTERNAL BATT.CHARGER, LI-ION BATT.BP290-SERIES
FOM	Fiber Optic Meter	TL	1265	FOM	FOM,FIBER OPTIC METER
FOS-850	Fiber Optic Light Source	TL	816	FOS-850	FOS-850,FIBER OPTIC SOURCE (850)
FOS-850/1300	Fiber Optic Light Source	TL	1969	FOS-850/1300	FOS-850/1300,FIBER OPTIC SOURCE (850/1300)
L200	Probe Light	TL	66	L200	L200,PROBE LIGHT
L205	Mini Hat Light	TL	75	L205	L205,MINI HAT LIGHT
L206	Deluxe Hat Light	TL	107	L206	L206,DELUXE LED HAT LIGHT
L210	Probe light and probe extender	TL	96	L210	L210,PROBE LIGHT AND PROBE EXTENDER
L215	SureGrip kit with probe light and probe extender	TL	215	L215	L215,SUREGRIP KIT WITH PROBE LIGHT AND PROBE EXTENDER
MC50	MeterCleaner Wipes, 50-pack	TL	229	MC50	MC50,METERCLEANER WIPES, 50-PACK
MC6	MeterCleaner Wipes, 6-pack	TL	41	MC6	MC6,METERCLEANER WIPES, 6-PACK
PV350	Pressure Vacuum Module	TL	1054	PV350	PV350,PRESSURE/VACUUM MODULE
SV225	Stray Voltage Adapter	TL	137	SV225	SV225,STRAY VOLTAGE ELIMINATOR
TPAK	ToolPak, Meter Hanging Kit	TL	103	TPAK	TPAK,METER HANGING KIT

Sigortalar

943121	Fuse, A:440mA (F), V:1000V, IR:10kA, 10.3x34.9 mm	TL	14	FUSE	FUSE,0.440A,1000V,FAST,.406X1.375,BULK
803293	Fuse, A:11A (F), V:1000V, IR:20kA, 10.3x38.1 mm	TL	26	FUSE	FUSE,11A,1000V,FAST.406INX1 SINGLE FUSE
830828	Fuse, A:1A (F), V:600V, IR:10kA, 10.3x34.9 mm	TL	21	FUSE	FUSE,FUSE,.406X1.375,1A,600V,FAST
2279339	Fuse, A:315mA (f), V:1000V, IR:10kA, 6.35x32 mm	TL	34	7017240.0	7017240.0,315,FUSE,315 MA,1000 V AC/DC,FAST,6.35 X 32 MM,BULK
740670	Fuse, A:630mA (F), V:250V, IR:1500A, 5x20 mm	TL	9	FUSE	FUSE,FUSE,5X20MM,0.63A,250V,FAST

Yazılım

FVF-Basic	FlukeView Forms Basic + IR USB cable (189, 287, 289, 789, 1550B)	TL	359	FVF-BASIC	FVF-BASIC,FLUKEVIEW FORMS W/CABLE FOR 180 SERIES AND 789
-----------	------------------------------------------------------------------	----	-----	-----------	----------------------------------------------------------

Model	Açıklama	Para Birimi	Tavsiye edilen Son Kullanıcı Liste fiyatı	Parça numarı	Ürün Tanımı
FVF-SC2	FlukeView Forms Software + IR USB- Cable (180 Series, 1653, 789, 1550B)	TL	560	FVF-SC2	FVF-SC2,FLUKEVIEW FORMS WITH CABLE FOR USE WITH 18X, 28X DMMS
FVF-SC3	FlukeView Forms Software + Cable (Fluke 45)	TL	576	FVF-SC3	FVF-SC3,FLUKEVIEW FORMS W/CABLE FOR 45 DMM
FVF-SC4	FlukeView Forms Software + Cable (8845A/8846A)	TL	727	FVF-SC4	FVF-SC4,FLUKEVIEW FORMS W/CABLE FOR 8845/8846
FVF-SC5	FlukeView Forms Basic (8845A/8846A)	TL	313	FVF-SC5	FVF-SC5,FLUKEVIEW FORMS - BASIC FOR 8845/8846
FVF-UG	FlukeView Forms Upgrade	TL	286	FVF-UG	FVF-UG,FLUKEVIEW FORMS UPGRADE
IR189USB	IR Cable - USB (280/180 Series, 1653, 789, 1550B)	TL	133	IR189USB	IR189USB, USB CABLE FOR FLUKE-18X, 28X DMMS
SCC120E	FlukeView Software + USB Cable + Case (120 Series) - English	TL	940	SCC120E	SCC120E,SOFTWARE & CABLE CARR.CASE120 SERIES
SCC120F	FlukeView Software + USB Cable + Case (Fluke 123) - French	TL	940	SCC120F	SCC120F,SOFTWARE & CABLE CARRY CASE 120 SERIES
SCC190	FlukeView Software + Cable + Case (190 Series) - English, French, German	TL	1349	SCC190EFG	SCC190EFG,SW & CABLE CARRYING CASE
SW43W	FlukeView Software (Fluke 43B/430 Series)	TL	878	SW43W	SW43W,FLUKEVIEW 43 SOFTWARE
700SW	DPC/Track Software	TL	6443	FLUKE- 700SW	FLUKE-700SW,DPC/TRACK
FlukeView Software	FlukeView Software	TL	675	SW90W	SW90W,FLUKEVIEW SCOPEMETER

***Fluke haber vermeksizin listedeki ürünleri ve fiyatları degistirme hakkina sahiptir**

